

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641161

Luminaire Tested: ML5612LSNFL2597FS1E - 693TBZB - 600LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641161  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSNFL2597FS1E - 693TBZB - 600LM - 2700K  
Description: ML56 RR, 25D TIR OPTIC, 6" TUSCON BRONZE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 859.8 lumens  
Efficiency: N/A  
Efficacy: 83.5 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641161  
CATALOG NUMBER: ML5612LSNFL2597FS1E - 693TBZB - 600LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P641161

CATALOG NUMBER: ML5612LSNFL2597FS1E - 693TBZB - 600LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |   |  |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |   |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |   |  |  |  |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 1   | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 94  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 2   | 108 | 104 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 96  | 93  | 96  | 94  | 91  | 93  | 91  | 90  | 88  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 3   | 103 | 97  | 92  | 89  | 101 | 96  | 91  | 88  | 93  | 89  | 86  | 91  | 88  | 85  | 88  | 86  | 84  | 82  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 4   | 98  | 91  | 86  | 82  | 97  | 90  | 85  | 81  | 88  | 84  | 80  | 86  | 82  | 79  | 84  | 81  | 79  | 77  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 5   | 94  | 86  | 80  | 76  | 92  | 85  | 80  | 76  | 83  | 79  | 75  | 82  | 78  | 75  | 80  | 77  | 74  | 72  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 6   | 90  | 81  | 75  | 71  | 88  | 80  | 75  | 71  | 79  | 74  | 71  | 77  | 73  | 70  | 76  | 73  | 70  | 68  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 7   | 86  | 77  | 71  | 67  | 84  | 76  | 71  | 67  | 75  | 70  | 67  | 74  | 69  | 66  | 73  | 69  | 66  | 65  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 8   | 82  | 73  | 67  | 63  | 81  | 72  | 67  | 63  | 71  | 66  | 63  | 70  | 66  | 63  | 69  | 65  | 63  | 61  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 9   | 78  | 69  | 64  | 60  | 77  | 69  | 64  | 60  | 68  | 63  | 60  | 67  | 63  | 60  | 66  | 62  | 59  | 58  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 10  | 75  | 66  | 61  | 57  | 74  | 66  | 61  | 57  | 65  | 60  | 57  | 64  | 60  | 57  | 64  | 60  | 57  | 56  |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 125297 |
| 5°  | 114307 |
| 10° | 83432  |
| 15° | 47747  |
| 20° | 29128  |
| 25° | 23614  |
| 30° | 19440  |
| 35° | 15767  |
| 40° | 12481  |
| 45° | 9559   |
| 50° | 4861   |
| 55° | 1223   |
| 60° | 746    |
| 65° | 337    |
| 70° | 144    |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9559 cd/sqm



TEST NUMBER: P641161

CATALOG NUMBER: ML5612LSNFL2597FS1E - 693TBZB - 600LM - 2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 179.5  | 20.9      |
| 10°-20°   | 241.3  | 28.1      |
| 20°-30°   | 179.9  | 20.9      |
| 30°-40°   | 147.7  | 17.2      |
| 40°-50°   | 91.0   | 10.6      |
| 50°-60°   | 17.3   | 2.0       |
| 60°-70°   | 2.9    | 0.3       |
| 70°-80°   | 0.4    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 600.6  | 69.9      |
| 0°-40°    | 748.4  | 87.0      |
| 0°-60°    | 856.6  | 99.6      |
| 0°-90°    | 859.8  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 859.8  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2286 |      |
| 5°  | 2077 | 179  |
| 15° | 841  | 241  |
| 25° | 390  | 180  |
| 35° | 236  | 148  |
| 45° | 123  | 91   |
| 55° | 13   | 17   |
| 65° | 3    | 3    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P641161

CATALOG NUMBER: ML5612LSNFL2597FS1E - 693TBZB - 600LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2285.6 |
| 2.5°  | 2239.7 |
| 5°    | 2077.2 |
| 7.5°  | 1816.9 |
| 10°   | 1498.8 |
| 12.5° | 1152.6 |
| 15°   | 841.3  |
| 17.5° | 621.0  |
| 20°   | 499.3  |
| 22.5° | 436.4  |
| 25°   | 390.4  |
| 27.5° | 346.2  |
| 30°   | 307.1  |
| 32.5° | 270.5  |
| 35°   | 235.6  |
| 37.5° | 204.2  |
| 40°   | 174.4  |
| 42.5° | 148.9  |
| 45°   | 123.3  |
| 47.5° | 88.5   |
| 50°   | 57.0   |
| 52.5° | 25.5   |
| 55°   | 12.8   |
| 57.5° | 8.5    |
| 60°   | 6.8    |
| 62.5° | 4.3    |
| 65°   | 2.6    |
| 67.5° | 0.9    |
| 70°   | 0.9    |
| 72.5° | 0.9    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)