

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641172

Luminaire Tested: ML5612LSNFL2597FS1E - 693WB - 1200LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641172
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSNFL2597FS1E - 693WB - 1200LM - 3000K
Description: ML56 RR, 25D TIR OPTIC, 6" WHITE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1449.5 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641172

CATALOG NUMBER: ML5612LSNFL2597FS1E - 693WB - 1200LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P641172

CATALOG NUMBER: ML5612LSNFL2597FS1E - 693WB - 1200LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	71	65	61	70	65	61	68	64	61	68	63	60	59																			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	60	57	56																			
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	200872
5°	183320
10°	134773
15°	76800
20°	47318
25°	38621
30°	31821
35°	26093
40°	20903
45°	16428
50°	9381
55°	3374
60°	2829
65°	2465
70°	2180
75°	2309
80°	2589
85°	2579

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16428 cd/sqm



TEST NUMBER: P641172

CATALOG NUMBER: ML5612LSNFL2597FS1E - 693WB - 1200LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	288.3	19.9
10°-20°	390.2	26.9
20°-30°	293.9	20.3
30°-40°	244.0	16.8
40°-50°	157.2	10.8
50°-60°	41.7	2.9
60°-70°	18.6	1.3
70°-80°	11.5	0.8
80°-90°	4.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	972.4	67.1
0°-40°	1216.4	83.9
0°-60°	1415.3	97.6
0°-90°	1449.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1449.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3664	
5°	3331	288
15°	1353	390
25°	638	294
35°	390	244
45°	212	157
55°	35	42
65°	19	19
75°	11	11
85°	4	4
90°	0	



TEST NUMBER: P641172

CATALOG NUMBER: ML5612LSNFL2597FS1E - 693WB - 1200LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3664.2
2.5°	3592.2
5°	3331.3
7.5°	2916.9
10°	2421.1
12.5°	1859.9
15°	1353.2
17.5°	1012.2
20°	811.1
22.5°	711.9
25°	638.5
27.5°	567.9
30°	502.7
32.5°	444.3
35°	389.9
37.5°	338.3
40°	292.1
42.5°	251.3
45°	211.9
47.5°	157.6
50°	110.0
52.5°	57.1
55°	35.3
57.5°	28.5
60°	25.8
62.5°	21.7
65°	19.0
67.5°	14.9
70°	13.6
72.5°	12.2
75°	10.9
77.5°	9.5
80°	8.2
82.5°	5.4
85°	4.1
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)