

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641201

Luminaire Tested: ML5612LSNFL2597FS1E - 694WB - 1200LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641201  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSNFL2597FS1E - 694WB - 1200LM - 2700K  
Description: ML56 RR, 25D TIR OPTIC, 6" WHITE GIMBAL TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1446.2 lumens  
Efficiency: N/A  
Efficacy: 87.7 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 16.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641201

CATALOG NUMBER: ML5612LSNFL2597FS1E - 694WB - 1200LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P641201

CATALOG NUMBER: ML5612LSNFL2597FS1E - 694WB - 1200LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78																			
4	96	88	82	78	94	87	81	77	85	80	76	82	78	75	81	77	74	73																			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																			
6	87	77	71	67	85	77	71	66	75	70	66	74	69	66	72	68	65	64																			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60																			
8	79	69	63	59	77	69	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	66	60	56	74	65	60	56	64	59	55	63	59	55	62	58	55	54																			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	194617
5°	177707
10°	128978
15°	73428
20°	44979
25°	36256
30°	29587
35°	23764
40°	18800
45°	14839
50°	11599
55°	9089
60°	7236
65°	5824
70°	4231
75°	2245
80°	1673
85°	818

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14839 cd/sqm



TEST NUMBER: P641201

CATALOG NUMBER: ML5612LSNFL2597FS1E - 694WB - 1200LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	278.4	19.3
10°-20°	372.6	25.8
20°-30°	276.2	19.1
30°-40°	223.0	15.4
40°-50°	149.2	10.3
50°-60°	86.6	6.0
60°-70°	45.3	3.1
70°-80°	13.2	0.9
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	927.2	64.1
0°-40°	1150.1	79.5
0°-60°	1386.0	95.8
0°-90°	1446.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1446.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3550	
5°	3229	278
15°	1294	373
25°	599	276
35°	355	223
45°	191	149
55°	95	87
65°	45	45
75°	11	13
85°	1	2
90°	0	



TEST NUMBER: P641201

CATALOG NUMBER: ML5612LSNFL2597FS1E - 694WB - 1200LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3550.1
2.5°	3476.1
5°	3229.3
7.5°	2817.3
10°	2317.0
12.5°	1784.9
15°	1293.8
17.5°	958.5
20°	771.0
22.5°	672.0
25°	599.4
27.5°	530.7
30°	467.4
32.5°	409.3
35°	355.1
37.5°	306.3
40°	262.7
42.5°	225.8
45°	191.4
47.5°	161.1
50°	136.0
52.5°	113.5
55°	95.1
57.5°	79.2
60°	66.0
62.5°	55.4
65°	44.9
67.5°	37.0
70°	26.4
72.5°	17.2
75°	10.6
77.5°	6.6
80°	5.3
82.5°	2.6
85°	1.3
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)