

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640713

Luminaire Tested: ML5612LSFL4097FS1E - 596WB - 600LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640713
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-35)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 596WB - 600LM - 3500K
Description: ML56 RR, 40D TIR OPTIC, 5" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1027.9 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.7
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640713
CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 600LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P640713

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 600LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																			
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71																			
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67																			
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63																			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59																			
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56																			
10	73	64	58	55	72	64	58	55	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	130876
5°	126820
10°	110627
15°	91116
20°	71221
25°	54195
30°	39342
35°	27032
40°	17694
45°	11443
50°	6509
55°	2725
60°	1847
65°	1009
70°	623
75°	549
80°	409
85°	815

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11443 cd/sqm



TEST NUMBER: P640713

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 600LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.5	14.2
10°-20°	307.9	29.9
20°-30°	285.0	27.7
30°-40°	178.0	17.3
40°-50°	80.4	7.8
50°-60°	22.4	2.2
60°-70°	6.2	0.6
70°-80°	1.9	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	738.3	71.8
0°-40°	916.4	89.2
0°-60°	1019.2	99.2
0°-90°	1027.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1027.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1658	
5°	1600	145
15°	1115	308
25°	622	285
35°	280	178
45°	102	80
55°	20	22
65°	5	6
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P640713

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 600LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1657.9
2.5°	1648.0
5°	1600.4
7.5°	1504.2
10°	1380.1
12.5°	1247.0
15°	1114.9
17.5°	977.3
20°	847.8
22.5°	729.2
25°	622.2
27.5°	520.6
30°	431.6
32.5°	350.6
35°	280.5
37.5°	221.2
40°	171.7
42.5°	133.1
45°	102.5
47.5°	73.7
50°	53.0
52.5°	35.1
55°	19.8
57.5°	14.4
60°	11.7
62.5°	9.0
65°	5.4
67.5°	3.6
70°	2.7
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)