

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641214

Luminaire Tested: ML5612LSNFL2597FS1E - 694WB - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641214
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSNFL2597FS1E - 694WB - 900LM - 4000K
Description: ML56 RR, 25D TIR OPTIC, 6" WHITE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1358.2 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641214
CATALOG NUMBER: ML5612LSNFL2597FS1E - 694WB - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641214

CATALOG NUMBER: ML5612LSNFL2597FS1E - 694WB - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92					92			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85					85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78					78			
4	96	88	82	78	94	87	81	77	85	80	76	82	78	75	81	77	74	73					73			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68					68			
6	87	77	71	67	85	77	71	66	75	70	66	74	69	66	72	68	65	64					64			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60					60			
8	79	69	63	59	77	69	63	59	67	62	58	66	62	58	65	61	58	57					57			
9	75	66	60	56	74	65	60	56	64	59	55	63	59	55	62	58	55	54					54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51					51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	182765
5°	166883
10°	121123
15°	68956
20°	42243
25°	34048
30°	27783
35°	22319
40°	17655
45°	13939
50°	10891
55°	8535
60°	6798
65°	5474
70°	3975
75°	2097
80°	1578
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13939 cd/sqm



TEST NUMBER: P641214

CATALOG NUMBER: ML5612LSNFL2597FS1E - 694WB - 900LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.5	19.3
10°-20°	349.9	25.8
20°-30°	259.4	19.1
30°-40°	209.4	15.4
40°-50°	140.1	10.3
50°-60°	81.3	6.0
60°-70°	42.6	3.1
70°-80°	12.4	0.9
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	870.7	64.1
0°-40°	1080.1	79.5
0°-60°	1301.5	95.8
0°-90°	1358.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1358.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3334	
5°	3033	261
15°	1215	350
25°	563	259
35°	334	209
45°	180	140
55°	89	81
65°	42	43
75°	10	12
85°	1	2
90°	0	



TEST NUMBER: P641214

CATALOG NUMBER: ML5612LSNFL2597FS1E - 694WB - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3333.9
2.5°	3264.4
5°	3032.6
7.5°	2645.8
10°	2175.9
12.5°	1676.2
15°	1215.0
17.5°	900.1
20°	724.1
22.5°	631.1
25°	562.9
27.5°	498.4
30°	438.9
32.5°	384.3
35°	333.5
37.5°	287.6
40°	246.7
42.5°	212.0
45°	179.8
47.5°	151.3
50°	127.7
52.5°	106.6
55°	89.3
57.5°	74.4
60°	62.0
62.5°	52.1
65°	42.2
67.5°	34.7
70°	24.8
72.5°	16.1
75°	9.9
77.5°	6.2
80°	5.0
82.5°	2.5
85°	1.2
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)