

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640717

Luminaire Tested: ML5612LSFL4097FS1E - 596WB - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640717
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-35)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 596WB - 900LM - 3000K
Description: ML56 RR, 40D TIR OPTIC, 5" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1283.7 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.7
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640717

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P640717

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																			
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71																			
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67																			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59																			
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56																			
10	73	64	58	55	72	64	58	55	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	163463
5°	158390
10°	138170
15°	113795
20°	88955
25°	67687
30°	49132
35°	33768
40°	22104
45°	14290
50°	8142
55°	3399
60°	2305
65°	1251
70°	785
75°	671
80°	500
85°	996

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14290 cd/sqm



TEST NUMBER: P640717

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.7	14.2
10°-20°	384.5	30.0
20°-30°	355.9	27.7
30°-40°	222.4	17.3
40°-50°	100.4	7.8
50°-60°	28.0	2.2
60°-70°	7.7	0.6
70°-80°	2.3	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	922.1	71.8
0°-40°	1144.5	89.2
0°-60°	1272.9	99.2
0°-90°	1283.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1283.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2071	
5°	1999	182
15°	1392	384
25°	777	356
35°	350	222
45°	128	100
55°	25	28
65°	7	8
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P640717

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2070.7
2.5°	2058.3
5°	1998.8
7.5°	1878.7
10°	1723.7
12.5°	1557.5
15°	1392.4
17.5°	1220.6
20°	1058.9
22.5°	910.7
25°	777.1
27.5°	650.2
30°	539.0
32.5°	437.9
35°	350.4
37.5°	276.2
40°	214.5
42.5°	166.2
45°	128.0
47.5°	92.1
50°	66.3
52.5°	43.8
55°	24.7
57.5°	18.0
60°	14.6
62.5°	11.2
65°	6.7
67.5°	4.5
70°	3.4
72.5°	2.2
75°	2.2
77.5°	2.2
80°	1.1
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)