

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640718

Luminaire Tested: ML5612LSFL4097FS1E - 596WB - 900LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-35)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 596WB - 900LM - 3500K
Description: ML56 RR, 40D TIR OPTIC, 5" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1318.8 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.7
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640718

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 900LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P640718

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 900LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|---|
| RF | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | 20 | |
| RC | 80 | | | | | 70 | | | | | 50 | | | | | 30 | | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 | |
| 1 | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 94 | | | 94 | |
| 2 | 108 | 103 | 99 | 96 | 106 | 101 | 98 | 95 | 98 | 95 | 93 | 95 | 93 | 91 | 93 | 91 | 89 | 87 | | | 87 | |
| 3 | 103 | 96 | 91 | 88 | 101 | 95 | 90 | 87 | 92 | 89 | 85 | 90 | 87 | 84 | 88 | 85 | 83 | 81 | | | 81 | |
| 4 | 98 | 90 | 85 | 81 | 96 | 89 | 84 | 80 | 87 | 83 | 79 | 85 | 81 | 78 | 83 | 80 | 77 | 76 | | | 76 | |
| 5 | 93 | 85 | 79 | 75 | 91 | 84 | 78 | 74 | 82 | 77 | 74 | 80 | 76 | 73 | 79 | 75 | 72 | 71 | | | 71 | |
| 6 | 88 | 80 | 74 | 70 | 87 | 79 | 73 | 69 | 77 | 73 | 69 | 76 | 72 | 68 | 75 | 71 | 68 | 67 | | | 67 | |
| 7 | 84 | 75 | 69 | 65 | 83 | 74 | 69 | 65 | 73 | 68 | 65 | 72 | 68 | 64 | 71 | 67 | 64 | 63 | | | 63 | |
| 8 | 80 | 71 | 65 | 61 | 79 | 71 | 65 | 61 | 69 | 64 | 61 | 68 | 64 | 61 | 67 | 63 | 60 | 59 | | | 59 | |
| 9 | 77 | 67 | 62 | 58 | 76 | 67 | 61 | 58 | 66 | 61 | 57 | 65 | 61 | 57 | 64 | 60 | 57 | 56 | | | 56 | |
| 10 | 73 | 64 | 58 | 55 | 72 | 64 | 58 | 55 | 63 | 58 | 54 | 62 | 57 | 54 | 61 | 57 | 54 | 53 | | | 53 | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 167915 |
| 5° | 162701 |
| 10° | 141929 |
| 15° | 116892 |
| 20° | 91383 |
| 25° | 69525 |
| 30° | 50471 |
| 35° | 34683 |
| 40° | 22702 |
| 45° | 14681 |
| 50° | 8363 |
| 55° | 3496 |
| 60° | 2368 |
| 65° | 1289 |
| 70° | 808 |
| 75° | 702 |
| 80° | 546 |
| 85° | 1087 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14681 cd/sqm



TEST NUMBER: P640718

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 900LM - 3500K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 186.6 | 14.2 |
| 10°-20° | 395.0 | 29.9 |
| 20°-30° | 365.6 | 27.7 |
| 30°-40° | 228.4 | 17.3 |
| 40°-50° | 103.1 | 7.8 |
| 50°-60° | 28.8 | 2.2 |
| 60°-70° | 7.9 | 0.6 |
| 70°-80° | 2.4 | 0.2 |
| 80°-90° | 0.8 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 947.2 | 71.8 |
| 0°-40° | 1175.7 | 89.1 |
| 0°-60° | 1307.6 | 99.2 |
| 0°-90° | 1318.8 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1318.8 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2127 | |
| 5° | 2053 | 187 |
| 15° | 1430 | 395 |
| 25° | 798 | 366 |
| 35° | 360 | 228 |
| 45° | 132 | 103 |
| 55° | 25 | 29 |
| 65° | 7 | 8 |
| 75° | 2 | 2 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P640718

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 900LM - 3500K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2127.1 |
| 2.5° | 2114.4 |
| 5° | 2053.2 |
| 7.5° | 1929.8 |
| 10° | 1770.6 |
| 12.5° | 1599.9 |
| 15° | 1430.3 |
| 17.5° | 1253.9 |
| 20° | 1087.8 |
| 22.5° | 935.5 |
| 25° | 798.2 |
| 27.5° | 667.9 |
| 30° | 553.7 |
| 32.5° | 449.9 |
| 35° | 359.9 |
| 37.5° | 283.8 |
| 40° | 220.3 |
| 42.5° | 170.7 |
| 45° | 131.5 |
| 47.5° | 94.6 |
| 50° | 68.1 |
| 52.5° | 45.0 |
| 55° | 25.4 |
| 57.5° | 18.5 |
| 60° | 15.0 |
| 62.5° | 11.5 |
| 65° | 6.9 |
| 67.5° | 4.6 |
| 70° | 3.5 |
| 72.5° | 2.3 |
| 75° | 2.3 |
| 77.5° | 2.3 |
| 80° | 1.2 |
| 82.5° | 1.2 |
| 85° | 1.2 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)