

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640722

Luminaire Tested: ML5612LSFL4097FS1E - 691WB - 1200LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640722
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 691WB - 1200LM - 3000K
Description: ML56 RR, 40D TIR OPTIC, 6" DEADFRONT TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1555.5 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640722
CATALOG NUMBER: ML5612LSFL4097FS1E - 691WB - 1200LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P640722

CATALOG NUMBER: ML5612LSFL4097FS1E - 691WB - 1200LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94																			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	91	87	101	95	90	87	92	89	85	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																			
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71																			
6	88	80	74	70	87	79	73	69	77	72	69	76	72	68	75	71	68	67																			
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	61	67	63	60	59																			
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56																			
10	73	64	58	55	72	64	58	55	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138295
5°	134041
10°	116770
15°	95784
20°	74772
25°	56586
30°	40823
35°	28074
40°	18363
45°	12001
50°	7062
55°	3766
60°	2083
65°	1232
70°	657
75°	297
80°	442
85°	881

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12001 cd/sqm



TEST NUMBER: P640722

CATALOG NUMBER: ML5612LSFL4097FS1E - 691WB - 1200LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.2	14.2
10°-20°	466.5	30.0
20°-30°	428.7	27.6
30°-40°	266.1	17.1
40°-50°	121.7	7.8
50°-60°	38.3	2.5
60°-70°	9.8	0.6
70°-80°	2.2	0.1
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1116.5	71.8
0°-40°	1382.5	88.9
0°-60°	1542.6	99.2
0°-90°	1555.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1555.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2523	
5°	2436	221
15°	1688	467
25°	936	429
35°	420	266
45°	155	122
55°	39	38
65°	10	10
75°	1	2
85°	1	1
90°	0	



TEST NUMBER: P640722

CATALOG NUMBER: ML5612LSFL4097FS1E - 691WB - 1200LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2522.7
2.5°	2506.4
5°	2435.8
7.5°	2286.5
10°	2097.7
12.5°	1892.7
15°	1687.7
17.5°	1480.0
20°	1281.7
22.5°	1098.4
25°	935.5
27.5°	782.1
30°	644.9
32.5°	522.7
35°	419.5
37.5°	331.3
40°	256.6
42.5°	199.6
45°	154.8
47.5°	114.1
50°	82.8
52.5°	57.0
55°	39.4
57.5°	25.8
60°	19.0
62.5°	13.6
65°	9.5
67.5°	5.4
70°	4.1
72.5°	2.7
75°	1.4
77.5°	1.4
80°	1.4
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)