

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641264

Luminaire Tested: ML5612LSVWFL7597FS1E - 592SC - 1200LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641264
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-71)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 592SC - 1200LM - 4000K
Description: ML56 RR, 75D TIR OPTIC, 5" SPECULAR CLEAR TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1630.6 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.07
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641264

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592SC - 1200LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641264

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592SC - 1200LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	93	105	100	96	92	96	93	90	93	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78															
4	95	87	81	76	93	85	80	75	83	78	75	81	77	74	79	76	73	71				71															
5	89	80	74	69	88	79	73	69	77	72	68	76	71	68	74	70	67	65				65															
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60				60															
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55				55															
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51				51															
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48															
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44				44															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96482
5°	96486
10°	98451
15°	101234
20°	100145
25°	94810
30°	85675
35°	68730
40°	45795
45°	23132
50°	12907
55°	7652
60°	2842
65°	560
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23132 cd/sqm



TEST NUMBER: P641264

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592SC - 1200LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.6	7.2
10°-20°	347.5	21.3
20°-30°	496.6	30.5
30°-40°	436.4	26.8
40°-50°	176.9	10.8
50°-60°	51.1	3.1
60°-70°	5.5	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	960.7	58.9
0°-40°	1397.1	85.7
0°-60°	1625.1	99.7
0°-90°	1630.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1630.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1222	
5°	1218	117
15°	1239	347
25°	1088	497
35°	713	436
45°	207	177
55°	56	51
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P641264

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592SC - 1200LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1222.2
2.5°	1222.2
5°	1217.6
7.5°	1220.7
10°	1228.2
12.5°	1237.2
15°	1238.7
17.5°	1223.7
20°	1192.1
22.5°	1145.6
25°	1088.5
27.5°	1021.0
30°	939.9
32.5°	836.3
35°	713.2
37.5°	576.5
40°	444.4
42.5°	313.8
45°	207.2
47.5°	136.6
50°	105.1
52.5°	78.1
55°	55.6
57.5°	36.0
60°	18.0
62.5°	9.0
65°	3.0
67.5°	1.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)