

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641301

Luminaire Tested: ML5612LSVWFL7597FS1E - 593BB - 900LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641301
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-75)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 593BB - 900LM - 2700K
Description: ML56 RR, 75D TIR OPTIC, 5" BLACK BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1120.4 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641301

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593BB - 900LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P641301

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593BB - 900LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85	85	85	85
3	101	94	88	84	99	92	87	83	90	85	82	87	83	81	85	82	79	78	78	78	78
4	95	87	80	76	93	85	80	75	83	78	74	81	77	74	79	76	73	71	71	71	71
5	89	80	74	69	88	79	73	69	77	72	68	76	71	67	74	70	67	65	65	65	65
6	84	74	68	63	83	74	67	63	72	66	62	71	66	62	69	65	61	60	60	60	60
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55	55	55	55
8	75	64	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	49	70	60	54	49	59	53	49	58	53	49	57	52	49	47	47	47	47
10	67	56	50	46	66	56	50	46	55	50	46	54	49	46	54	49	45	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62821
5°	63758
10°	65714
15°	68339
20°	69239
25°	65892
30°	59104
35°	47655
40°	31946
45°	15964
50°	8977
55°	5409
60°	1895
65°	205
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15964 cd/sqm



TEST NUMBER: P641301

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593BB - 900LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.3	6.9
10°-20°	235.6	21.0
20°-30°	344.4	30.7
30°-40°	301.6	26.9
40°-50°	122.5	10.9
50°-60°	35.7	3.2
60°-70°	3.3	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	657.3	58.7
0°-40°	959.0	85.6
0°-60°	1117.1	99.7
0°-90°	1120.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1120.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	796	
5°	805	77
15°	836	236
25°	756	344
35°	494	302
45°	143	122
55°	39	36
65°	1	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P641301

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593BB - 900LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	795.8
2.5°	798.0
5°	804.6
7.5°	812.2
10°	819.8
12.5°	828.6
15°	836.2
17.5°	836.2
20°	824.2
22.5°	796.9
25°	756.5
27.5°	707.4
30°	648.4
32.5°	575.3
35°	494.5
37.5°	398.5
40°	310.0
42.5°	216.1
45°	143.0
47.5°	95.0
50°	73.1
52.5°	54.6
55°	39.3
57.5°	25.1
60°	12.0
62.5°	6.5
65°	1.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)