

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640750

Luminaire Tested: ML5612LSFL4097FS1E - 692H - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640750
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-38)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 692H - 900LM - 5000K
Description: ML56 RR, 40D TIR OPTIC, 6" HAZE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1416.9 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640750
CATALOG NUMBER: ML5612LSFL4097FS1E - 692H - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P640750

CATALOG NUMBER: ML5612LSFL4097FS1E - 692H - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	114	111	109	106	111	109	107	105	105	103	102	101	100	98	98	97	96	94						94													
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88						88													
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82						82													
4	98	91	85	81	96	90	85	81	87	83	80	86	82	79	84	81	78	77						77													
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72						72													
6	89	80	75	70	87	80	74	70	78	73	70	77	72	69	75	72	69	67						67													
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63						63													
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60						60													
9	77	68	62	59	76	68	62	58	67	62	58	66	61	58	65	61	58	57						57													
10	74	65	59	55	73	64	59	55	64	59	55	63	58	55	62	58	55	54						54													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128400
5°	124312
10°	108198
15°	88831
20°	69154
25°	52479
30°	38031
35°	26000
40°	16789
45°	10296
50°	5185
55°	2131
60°	1360
65°	480
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10296 cd/sqm



TEST NUMBER: P640750

CATALOG NUMBER: ML5612LSFL4097FS1E - 692H - 900LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.2	14.5
10°-20°	432.2	30.5
20°-30°	397.9	28.1
30°-40°	246.5	17.4
40°-50°	106.6	7.5
50°-60°	24.0	1.7
60°-70°	4.5	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1035.4	73.1
0°-40°	1281.9	90.5
0°-60°	1412.4	99.7
0°-90°	1416.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1416.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2342	
5°	2259	205
15°	1565	432
25°	868	398
35°	388	246
45°	133	107
55°	22	24
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640750

CATALOG NUMBER: ML5612LSFL4097FS1E - 692H - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2342.2
2.5°	2326.0
5°	2259.0
7.5°	2121.2
10°	1943.7
12.5°	1756.3
15°	1565.2
17.5°	1369.1
20°	1185.4
22.5°	1017.8
25°	867.6
27.5°	728.6
30°	600.8
32.5°	487.8
35°	388.5
37.5°	304.1
40°	234.6
42.5°	181.2
45°	132.8
47.5°	98.1
50°	60.8
52.5°	32.3
55°	22.3
57.5°	17.4
60°	12.4
62.5°	7.4
65°	3.7
67.5°	1.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)