

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640757

Luminaire Tested: ML5612LSFL4097FS1E - 692SC - 600LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640757
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-37)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 692SC - 600LM - 3000K
Description: ML56 RR, 40D TIR OPTIC, 6" SPECULAR CLEAR TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1001.5 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.66
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640757
CATALOG NUMBER: ML5612LSFL4097FS1E - 692SC - 600LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P640757
 CATALOG NUMBER: ML5612LSFL4097FS1E - 692SC - 600LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82																			
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77																			
5	94	86	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72																			
6	89	81	75	71	88	80	74	71	78	74	70	77	73	70	76	72	69	68																			
7	85	76	70	66	84	76	70	66	74	69	66	73	69	66	72	68	65	64																			
8	81	72	66	62	80	72	66	62	71	66	62	69	65	62	69	65	62	60																			
9	78	68	63	59	77	68	63	59	67	62	59	66	62	59	65	61	58	57																			
10	74	65	60	56	73	65	59	56	64	59	56	63	59	56	62	58	55	54																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100047
5°	91811
10°	77487
15°	62861
20°	48689
25°	36885
30°	26580
35°	18150
40°	11643
45°	7125
50°	3727
55°	1424
60°	866
65°	337
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7125 cd/sqm



TEST NUMBER: P640757

CATALOG NUMBER: ML5612LSFL4097FS1E - 692SC - 600LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.7	15.1
10°-20°	306.3	30.6
20°-30°	279.6	27.9
30°-40°	171.9	17.2
40°-50°	73.8	7.4
50°-60°	16.3	1.6
60°-70°	2.9	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	736.6	73.6
0°-40°	908.5	90.7
0°-60°	998.6	99.7
0°-90°	1001.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1001.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1825	
5°	1668	151
15°	1108	306
25°	610	280
35°	271	172
45°	92	74
55°	15	16
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640757

CATALOG NUMBER: ML5612LSFL4097FS1E - 692SC - 600LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1825.0
2.5°	1786.5
5°	1668.4
7.5°	1538.9
10°	1392.0
12.5°	1248.5
15°	1107.6
17.5°	966.8
20°	834.6
22.5°	716.5
25°	609.8
27.5°	510.9
30°	419.9
32.5°	340.3
35°	271.2
37.5°	211.7
40°	162.7
42.5°	125.1
45°	91.9
47.5°	67.4
50°	43.7
52.5°	21.9
55°	14.9
57.5°	11.4
60°	7.9
62.5°	5.2
65°	2.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)