

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641304

Luminaire Tested: ML5612LSVWFL7597FS1E - 593BB - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-75)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 593BB - 900LM - 4000K
Description: ML56 RR, 75D TIR OPTIC, 5" BLACK BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1273.8 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641304

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593BB - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641304

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593BB - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92																
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85			85																
3	101	94	88	84	99	92	87	83	90	85	82	87	83	81	85	82	79	78			78																
4	95	87	80	76	93	85	80	75	83	78	74	81	77	74	79	76	73	71			71																
5	89	80	74	69	88	79	73	69	77	72	68	76	71	67	74	70	67	65			65																
6	84	74	68	63	83	74	67	63	72	66	62	71	66	62	69	65	61	60			60																
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55			55																
8	75	64	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51																
9	71	60	54	49	70	60	54	49	59	53	49	58	53	49	57	52	49	47			47																
10	67	56	50	46	66	56	50	46	55	50	46	54	49	46	54	49	45	44			44																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71418
5°	72475
10°	74708
15°	77688
20°	78715
25°	74907
30°	67198
35°	54179
40°	36325
45°	18153
50°	10206
55°	6152
60°	2163
65°	224
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18153 cd/sqm



TEST NUMBER: P641304

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593BB - 900LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	6.9
10°-20°	267.9	21.0
20°-30°	391.6	30.7
30°-40°	342.9	26.9
40°-50°	139.2	10.9
50°-60°	40.6	3.2
60°-70°	3.7	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	747.3	58.7
0°-40°	1090.2	85.6
0°-60°	1270.1	99.7
0°-90°	1273.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1273.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	905	
5°	915	88
15°	951	268
25°	860	392
35°	562	343
45°	163	139
55°	45	41
65°	1	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P641304

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593BB - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	904.7
2.5°	907.2
5°	914.6
7.5°	923.3
10°	932.0
12.5°	941.9
15°	950.6
17.5°	950.6
20°	937.0
22.5°	906.0
25°	860.0
27.5°	804.2
30°	737.2
32.5°	654.0
35°	562.2
37.5°	453.0
40°	352.5
42.5°	245.7
45°	162.6
47.5°	108.0
50°	83.1
52.5°	62.1
55°	44.7
57.5°	28.5
60°	13.7
62.5°	7.4
65°	1.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)