

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641314

Luminaire Tested: ML5612LSVWFL7597FS1E - 593SNB - 600LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641314
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 593SNB - 600LM - 4000K
Description: ML56 RR, 75D TIR OPTIC, 5" SATIN NICKLE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1019.9 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641314

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593SNB - 600LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641314

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593SNB - 600LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92																											
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84																											
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77																											
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71																											
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	74	69	66	65																											
6	84	74	67	63	82	73	67	62	72	66	62	70	65	61	69	64	61	59																											
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55																											
8	75	64	57	53	73	63	57	53	62	57	52	61	56	52	60	55	52	50																											
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47																											
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	43																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56261
5°	57086
10°	58836
15°	61090
20°	62064
25°	59125
30°	53060
35°	42961
40°	28998
45°	15216
50°	8793
55°	5450
60°	2447
65°	728
70°	439
75°	305
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15216 cd/sqm



TEST NUMBER: P641314

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593SNB - 600LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.2	6.8
10°-20°	210.8	20.7
20°-30°	308.9	30.3
30°-40°	272.9	26.8
40°-50°	115.2	11.3
50°-60°	36.4	3.6
60°-70°	5.4	0.5
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	589.0	57.7
0°-40°	861.8	84.5
0°-60°	1013.5	99.4
0°-90°	1019.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1019.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	713	
5°	720	69
15°	748	211
25°	679	309
35°	446	273
45°	136	115
55°	40	36
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P641314

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593SNB - 600LM - 4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	712.7
2.5°	714.6
5°	720.4
7.5°	727.2
10°	734.0
12.5°	740.7
15°	747.5
17.5°	748.5
20°	738.8
22.5°	713.6
25°	678.8
27.5°	635.3
30°	582.1
32.5°	520.2
35°	445.8
37.5°	363.6
40°	281.4
42.5°	202.1
45°	136.3
47.5°	91.9
50°	71.6
52.5°	54.2
55°	39.6
57.5°	27.1
60°	15.5
62.5°	7.7
65°	3.9
67.5°	1.9
70°	1.9
72.5°	1.0
75°	1.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)