

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640759

Luminaire Tested: ML5612LSFL4097FS1E - 692SC - 600LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640759
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-37)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 692SC - 600LM - 4000K
Description: ML56 RR, 40D TIR OPTIC, 6" SPECULAR CLEAR TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1107.0 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.66
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640759
CATALOG NUMBER: ML5612LSFL4097FS1E - 692SC - 600LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P640759

CATALOG NUMBER: ML5612LSFL4097FS1E - 692SC - 600LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82																			
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77																			
5	94	86	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72																			
6	89	81	75	71	88	80	74	71	78	74	70	77	73	70	76	72	69	68																			
7	85	76	70	66	84	76	70	66	74	69	66	73	69	66	72	68	65	64																			
8	81	72	66	62	80	72	66	62	71	66	62	69	65	62	69	65	62	60																			
9	78	68	63	59	77	68	63	59	67	62	59	66	62	59	65	61	58	57																			
10	74	65	60	56	73	65	59	56	64	59	56	63	59	56	62	58	55	54																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110578
5°	101475
10°	85642
15°	69478
20°	53817
25°	40768
30°	29378
35°	20064
40°	12874
45°	7869
50°	4119
55°	1567
60°	954
65°	376
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7869 cd/sqm



TEST NUMBER: P640759

CATALOG NUMBER: ML5612LSFL4097FS1E - 692SC - 600LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.6	15.1
10°-20°	338.5	30.6
20°-30°	309.0	27.9
30°-40°	190.0	17.2
40°-50°	81.6	7.4
50°-60°	18.0	1.6
60°-70°	3.2	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.2	73.6
0°-40°	1004.2	90.7
0°-60°	1103.8	99.7
0°-90°	1107.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1107.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2017	
5°	1844	167
15°	1224	339
25°	674	309
35°	300	190
45°	102	82
55°	16	18
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640759

CATALOG NUMBER: ML5612LSFL4097FS1E - 692SC - 600LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2017.1
2.5°	1974.6
5°	1844.0
7.5°	1700.9
10°	1538.5
12.5°	1379.9
15°	1224.2
17.5°	1068.5
20°	922.5
22.5°	792.0
25°	674.0
27.5°	564.7
30°	464.1
32.5°	376.2
35°	299.8
37.5°	234.0
40°	179.9
42.5°	138.3
45°	101.5
47.5°	74.5
50°	48.3
52.5°	24.2
55°	16.4
57.5°	12.6
60°	8.7
62.5°	5.8
65°	2.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)