

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640762

Luminaire Tested: ML5612LSFL4097FS1E - 692SC - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640762
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-37)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 692SC - 900LM - 3000K
Description: ML56 RR, 40D TIR OPTIC, 6" SPECULAR CLEAR TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1284.9 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.66
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640762
CATALOG NUMBER: ML5612LSFL4097FS1E - 692SC - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P640762

CATALOG NUMBER: ML5612LSFL4097FS1E - 692SC - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																												
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																												
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82																												
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77																												
5	94	86	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72																												
6	89	81	75	71	88	80	74	71	78	74	70	77	73	70	76	72	69	68																												
7	85	76	70	66	84	76	70	66	74	69	66	73	69	66	72	68	65	64																												
8	81	72	66	62	80	72	66	62	71	66	62	69	65	62	69	65	62	60																												
9	78	68	63	59	77	68	63	59	67	62	59	66	62	59	65	61	58	57																												
10	74	65	60	56	73	65	59	56	64	59	56	63	59	56	62	58	55	54																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128356
5°	117791
10°	99408
15°	80647
20°	62469
25°	47325
30°	34107
35°	23289
40°	14942
45°	9140
50°	4784
55°	1826
60°	1107
65°	441
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9140 cd/sqm



TEST NUMBER: P640762

CATALOG NUMBER: ML5612LSFL4097FS1E - 692SC - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.4	15.1
10°-20°	393.0	30.6
20°-30°	358.7	27.9
30°-40°	220.5	17.2
40°-50°	94.7	7.4
50°-60°	21.0	1.6
60°-70°	3.7	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	945.1	73.6
0°-40°	1165.6	90.7
0°-60°	1281.2	99.7
0°-90°	1284.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1284.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2341	
5°	2140	193
15°	1421	393
25°	782	359
35°	348	221
45°	118	95
55°	19	21
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640762

CATALOG NUMBER: ML5612LSFL4097FS1E - 692SC - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2341.4
2.5°	2292.1
5°	2140.5
7.5°	1974.4
10°	1785.8
12.5°	1601.7
15°	1421.0
17.5°	1240.3
20°	1070.8
22.5°	919.3
25°	782.4
27.5°	655.5
30°	538.8
32.5°	436.6
35°	348.0
37.5°	271.6
40°	208.8
42.5°	160.5
45°	117.9
47.5°	86.4
50°	56.1
52.5°	28.1
55°	19.1
57.5°	14.6
60°	10.1
62.5°	6.7
65°	3.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)