

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641344

Luminaire Tested: ML5612LSVWFL7597FS1E - 593WB - 600LM - 4000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641344  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-74)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL7597FS1E - 593WB - 600LM - 4000K  
Description: ML56 RR, 75D TIR OPTIC, 5" WHITE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1040.2 lumens  
Efficiency: N/A  
Efficacy: 101.0 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641344

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593WB - 600LM - 4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641344

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593WB - 600LM - 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59	59	59	59
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	62	56	52	61	55	51	60	55	51	50	50	50	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46	46	46	46
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43	43	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	56545
5°	57451
10°	59125
15°	61384
20°	62283
25°	59273
30°	53306
35°	42942
40°	29184
45°	15105
50°	9260
55°	6125
60°	3047
65°	1812
70°	1777
75°	1769
80°	1773
85°	1721

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 15105 cd/sqm



TEST NUMBER: P641344

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593WB - 600LM - 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.6	6.7
10°-20°	211.9	20.4
20°-30°	309.9	29.8
30°-40°	273.3	26.3
40°-50°	115.8	11.1
50°-60°	40.3	3.9
60°-70°	11.2	1.1
70°-80°	6.1	0.6
80°-90°	2.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	591.4	56.9
0°-40°	864.7	83.1
0°-60°	1020.8	98.1
0°-90°	1040.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1040.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	716	
5°	725	70
15°	751	212
25°	680	310
35°	446	273
45°	135	116
55°	44	40
65°	10	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P641344

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 593WB - 600LM - 4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	716.3
2.5°	719.2
5°	725.0
7.5°	731.8
10°	737.6
12.5°	745.3
15°	751.1
17.5°	752.1
20°	741.4
22.5°	716.3
25°	680.5
27.5°	637.0
30°	584.8
32.5°	521.0
35°	445.6
37.5°	363.5
40°	283.2
42.5°	201.1
45°	135.3
47.5°	93.8
50°	75.4
52.5°	58.0
55°	44.5
57.5°	31.9
60°	19.3
62.5°	13.5
65°	9.7
67.5°	8.7
70°	7.7
72.5°	6.8
75°	5.8
77.5°	4.8
80°	3.9
82.5°	2.9
85°	1.9
87.5°	1.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)