

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641352

Luminaire Tested: ML5612LSVWFL7597FS1E - 594SNB - 1200LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641352  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-79)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL7597FS1E - 594SNB - 1200LM - 3000K  
Description: ML56 RR, 75D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1490.3 lumens  
Efficiency: N/A  
Efficacy: 90.3 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 16.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641352

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 594SNB - 1200LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641352

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 594SNB - 1200LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91	
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83			83	
3	99	92	86	81	97	90	85	80	87	83	79	85	81	78	83	79	77	75			75	
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			68	
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			62	
6	82	72	65	60	81	71	64	60	69	64	59	68	63	59	67	62	58	57			57	
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			52	
8	73	62	55	50	72	61	55	50	60	54	50	59	54	50	58	53	50	48			48	
9	69	58	51	47	68	57	51	47	56	50	46	55	50	46	54	50	46	44			44	
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41			41	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	77394
5°	78656
10°	81097
15°	84341
20°	85553
25°	81492
30°	73150
35°	59016
40°	40725
45°	24259
50°	15339
55°	10460
60°	8147
65°	6594
70°	5332
75°	4148
80°	2455
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24259 cd/sqm



TEST NUMBER: P641352

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 594SNB - 1200LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.4	6.4
10°-20°	290.9	19.5
20°-30°	426.0	28.6
30°-40°	376.0	25.2
40°-50°	178.4	12.0
50°-60°	71.9	4.8
60°-70°	35.7	2.4
70°-80°	14.5	1.0
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	812.3	54.5
0°-40°	1188.3	79.7
0°-60°	1438.6	96.5
0°-90°	1490.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1490.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	980	
5°	993	95
15°	1032	291
25°	936	426
35°	612	376
45°	217	178
55°	76	72
65°	35	36
75°	14	14
85°	0	1
90°	0	



TEST NUMBER: P641352

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 594SNB - 1200LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	980.4
2.5°	984.5
5°	992.6
7.5°	1002.2
10°	1011.7
12.5°	1022.5
15°	1032.0
17.5°	1033.4
20°	1018.4
22.5°	984.5
25°	935.6
27.5°	875.9
30°	802.5
32.5°	714.3
35°	612.4
37.5°	501.1
40°	395.2
42.5°	297.4
45°	217.3
47.5°	161.6
50°	124.9
52.5°	96.4
55°	76.0
57.5°	62.5
60°	51.6
62.5°	42.1
65°	35.3
67.5°	29.9
70°	23.1
72.5°	17.7
75°	13.6
77.5°	9.5
80°	5.4
82.5°	2.7
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)