

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640768

Luminaire Tested: ML5612LSFL4097FS1E - 692W - 1200LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640768
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-39)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 692W - 1200LM - 3500K
Description: ML56 RR, 40D TIR OPTIC, 6" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1597.9 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640768

CATALOG NUMBER: ML5612LSFL4097FS1E - 692W - 1200LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P640768

CATALOG NUMBER: ML5612LSFL4097FS1E - 692W - 1200LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	98	96	95	94																			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	78	76																			
5	93	85	79	75	91	84	79	75	82	78	74	80	76	73	79	75	73	71																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63																			
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59																			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	60	57	56																			
10	74	64	59	55	73	64	58	55	63	58	55	62	58	55	62	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142735
5°	138366
10°	120561
15°	99013
20°	77287
25°	58794
30°	42639
35°	29212
40°	18964
45°	11784
50°	6183
55°	2800
60°	1831
65°	1090
70°	673
75°	593
80°	884
85°	881

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11784 cd/sqm



TEST NUMBER: P640768

CATALOG NUMBER: ML5612LSFL4097FS1E - 692W - 1200LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.4	14.3
10°-20°	481.8	30.2
20°-30°	445.6	27.9
30°-40°	277.0	17.3
40°-50°	121.7	7.6
50°-60°	29.9	1.9
60°-70°	8.8	0.5
70°-80°	3.5	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1155.9	72.3
0°-40°	1432.9	89.7
0°-60°	1584.4	99.2
0°-90°	1597.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1597.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2604	
5°	2514	228
15°	1745	482
25°	972	446
35°	436	277
45°	152	122
55°	29	30
65°	8	9
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P640768

CATALOG NUMBER: ML5612LSFL4097FS1E - 692W - 1200LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2603.7
2.5°	2586.9
5°	2514.4
7.5°	2362.4
10°	2165.8
12.5°	1956.6
15°	1744.6
17.5°	1525.7
20°	1324.8
22.5°	1138.0
25°	972.0
27.5°	817.2
30°	673.6
32.5°	546.7
35°	436.5
37.5°	343.1
40°	265.0
42.5°	205.0
45°	152.0
47.5°	113.0
50°	72.5
52.5°	39.0
55°	29.3
57.5°	22.3
60°	16.7
62.5°	12.6
65°	8.4
67.5°	4.2
70°	4.2
72.5°	4.2
75°	2.8
77.5°	2.8
80°	2.8
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)