

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641369

Luminaire Tested: ML5612LSVWFL7597FS1E - 594TBZB - 1200LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641369
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-80)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 594TBZB - 1200LM - 4000K
Description: ML56 RR, 75D TIR OPTIC, 5" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1644.1 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641369

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 594TBZB - 1200LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641369

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 594TBZB - 1200LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83																			
3	99	92	86	81	97	90	85	80	87	83	79	85	81	78	83	79	77	75																			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68																			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62																			
6	82	72	65	60	81	71	64	60	69	64	59	68	63	59	67	62	58	57																			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52																			
8	73	62	55	50	72	61	55	50	60	54	50	59	54	50	58	53	50	48																			
9	69	58	51	47	68	57	51	47	56	50	46	55	50	46	54	50	46	44																			
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85359
5°	86755
10°	89561
15°	93151
20°	94365
25°	89993
30°	80762
35°	64982
40°	44878
45°	26827
50°	16972
55°	11575
60°	9015
65°	7285
70°	5886
75°	4575
80°	2728
85°	1359

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26827 cd/sqm



TEST NUMBER: P641369

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 594TBZB - 1200LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.2	6.4
10°-20°	321.1	19.5
20°-30°	470.2	28.6
30°-40°	414.4	25.2
40°-50°	196.9	12.0
50°-60°	79.2	4.8
60°-70°	39.1	2.4
70°-80°	16.0	1.0
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	896.4	54.5
0°-40°	1310.8	79.7
0°-60°	1586.9	96.5
0°-90°	1644.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1644.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1081	
5°	1095	105
15°	1140	321
25°	1033	470
35°	674	414
45°	240	197
55°	84	79
65°	39	39
75°	15	16
85°	2	2
90°	0	



TEST NUMBER: P641369

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 594TBZB - 1200LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1081.3
2.5°	1085.8
5°	1094.8
7.5°	1105.3
10°	1117.3
12.5°	1127.8
15°	1139.8
17.5°	1139.8
20°	1123.3
22.5°	1085.8
25°	1033.2
27.5°	967.1
30°	886.0
32.5°	786.9
35°	674.3
37.5°	552.6
40°	435.5
42.5°	327.4
45°	240.3
47.5°	178.7
50°	138.2
52.5°	105.1
55°	84.1
57.5°	69.1
60°	57.1
62.5°	46.6
65°	39.0
67.5°	31.5
70°	25.5
72.5°	19.5
75°	15.0
77.5°	10.5
80°	6.0
82.5°	3.0
85°	1.5
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)