

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640776

Luminaire Tested: ML5612LSFL4097FS1E - 692W - 900LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P640776  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-39)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSFL4097FS1E - 692W - 900LM - 2700K  
Description: ML56 RR, 40D TIR OPTIC, 6" WHITE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1249.2 lumens  
Efficiency: N/A  
Efficacy: 93.9 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P640776  
CATALOG NUMBER: ML5612LSFL4097FS1E - 692W - 900LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P640776

CATALOG NUMBER: ML5612LSFL4097FS1E - 692W - 900LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 100 | 98  | 98  | 96  | 95  | 94  |    |    |   |
| 2   | 108 | 103 | 99  | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 93  | 95  | 93  | 91  | 93  | 91  | 89  | 87  |    |    |   |
| 3   | 103 | 96  | 92  | 88  | 101 | 95  | 91  | 87  | 92  | 89  | 86  | 90  | 87  | 84  | 88  | 85  | 83  | 81  |    |    |   |
| 4   | 98  | 90  | 85  | 81  | 96  | 89  | 84  | 80  | 87  | 83  | 79  | 85  | 81  | 78  | 83  | 80  | 78  | 76  |    |    |   |
| 5   | 93  | 85  | 79  | 75  | 91  | 84  | 79  | 75  | 82  | 78  | 74  | 80  | 76  | 73  | 79  | 75  | 73  | 71  |    |    |   |
| 6   | 89  | 80  | 74  | 70  | 87  | 79  | 74  | 70  | 78  | 73  | 69  | 76  | 72  | 69  | 75  | 71  | 68  | 67  |    |    |   |
| 7   | 84  | 75  | 70  | 65  | 83  | 75  | 69  | 65  | 73  | 69  | 65  | 72  | 68  | 65  | 71  | 67  | 64  | 63  |    |    |   |
| 8   | 81  | 71  | 66  | 62  | 79  | 71  | 65  | 61  | 70  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 59  |    |    |   |
| 9   | 77  | 68  | 62  | 58  | 76  | 67  | 62  | 58  | 66  | 61  | 58  | 65  | 61  | 58  | 65  | 60  | 57  | 56  |    |    |   |
| 10  | 74  | 64  | 59  | 55  | 73  | 64  | 58  | 55  | 63  | 58  | 55  | 62  | 58  | 55  | 62  | 57  | 54  | 53  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 111592 |
| 5°  | 108183 |
| 10° | 94259  |
| 15° | 77412  |
| 20° | 60427  |
| 25° | 45970  |
| 30° | 33334  |
| 35° | 22841  |
| 40° | 14828  |
| 45° | 9210   |
| 50° | 4836   |
| 55° | 2189   |
| 60° | 1436   |
| 65° | 843    |
| 70° | 529    |
| 75° | 466    |
| 80° | 695    |
| 85° | 692    |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9210 cd/sqm



TEST NUMBER: P640776

CATALOG NUMBER: ML5612LSFL4097FS1E - 692W - 900LM - 2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 178.6  | 14.3      |
| 10°-20°   | 376.7  | 30.2      |
| 20°-30°   | 348.4  | 27.9      |
| 30°-40°   | 216.6  | 17.3      |
| 40°-50°   | 95.1   | 7.6       |
| 50°-60°   | 23.4   | 1.9       |
| 60°-70°   | 6.8    | 0.5       |
| 70°-80°   | 2.8    | 0.2       |
| 80°-90°   | 0.9    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 903.7  | 72.3      |
| 0°-40°    | 1120.2 | 89.7      |
| 0°-60°    | 1238.8 | 99.2      |
| 0°-90°    | 1249.2 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1249.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2036 |      |
| 5°  | 1966 | 179  |
| 15° | 1364 | 377  |
| 25° | 760  | 348  |
| 35° | 341  | 217  |
| 45° | 119  | 95   |
| 55° | 23   | 23   |
| 65° | 6    | 7    |
| 75° | 2    | 3    |
| 85° | 1    | 1    |
| 90° | 0    |      |



TEST NUMBER: P640776

CATALOG NUMBER: ML5612LSFL4097FS1E - 692W - 900LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2035.6 |
| 2.5°  | 2022.6 |
| 5°    | 1965.9 |
| 7.5°  | 1847.0 |
| 10°   | 1693.3 |
| 12.5° | 1529.7 |
| 15°   | 1364.0 |
| 17.5° | 1192.8 |
| 20°   | 1035.8 |
| 22.5° | 889.7  |
| 25°   | 760.0  |
| 27.5° | 638.9  |
| 30°   | 526.6  |
| 32.5° | 427.4  |
| 35°   | 341.3  |
| 37.5° | 268.2  |
| 40°   | 207.2  |
| 42.5° | 160.3  |
| 45°   | 118.8  |
| 47.5° | 88.3   |
| 50°   | 56.7   |
| 52.5° | 30.5   |
| 55°   | 22.9   |
| 57.5° | 17.4   |
| 60°   | 13.1   |
| 62.5° | 9.8    |
| 65°   | 6.5    |
| 67.5° | 3.3    |
| 70°   | 3.3    |
| 72.5° | 3.3    |
| 75°   | 2.2    |
| 77.5° | 2.2    |
| 80°   | 2.2    |
| 82.5° | 1.1    |
| 85°   | 1.1    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)