

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641379

Luminaire Tested: ML5612LSVWFL7597FS1E - 594TBZB - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641379
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-80)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 594TBZB - 900LM - 4000K
Description: ML56 RR, 75D TIR OPTIC, 5" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1358.2 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641379
CATALOG NUMBER: ML5612LSVWFL7597FS1E - 594TBZB - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641379

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 594TBZB - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83																			
3	99	92	86	81	97	90	85	80	87	83	79	85	81	78	83	79	77	75																			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68																			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62																			
6	82	72	65	60	81	71	64	60	69	64	59	68	63	59	67	62	58	57																			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52																			
8	73	62	55	50	72	61	55	50	60	54	50	59	54	50	58	53	50	48																			
9	69	58	51	47	68	57	51	47	56	50	46	55	50	46	54	50	46	44																			
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70510
5°	71667
10°	73986
15°	76953
20°	77950
25°	74341
30°	66715
35°	53678
40°	37077
45°	22160
50°	14013
55°	9565
60°	7436
65°	6033
70°	4870
75°	3782
80°	2273
85°	1087

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22160 cd/sqm



TEST NUMBER: P641379

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 594TBZB - 900LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.9	6.4
10°-20°	265.2	19.5
20°-30°	388.4	28.6
30°-40°	342.4	25.2
40°-50°	162.6	12.0
50°-60°	65.4	4.8
60°-70°	32.3	2.4
70°-80°	13.2	1.0
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	740.5	54.5
0°-40°	1082.9	79.7
0°-60°	1310.9	96.5
0°-90°	1358.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1358.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	893	
5°	904	87
15°	942	265
25°	854	388
35°	557	342
45°	198	163
55°	70	65
65°	32	32
75°	12	13
85°	1	2
90°	0	



TEST NUMBER: P641379

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 594TBZB - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	893.2
2.5°	896.9
5°	904.4
7.5°	913.0
10°	923.0
12.5°	931.7
15°	941.6
17.5°	941.6
20°	927.9
22.5°	896.9
25°	853.5
27.5°	798.9
30°	731.9
32.5°	650.1
35°	557.0
37.5°	456.5
40°	359.8
42.5°	270.4
45°	198.5
47.5°	147.6
50°	114.1
52.5°	86.8
55°	69.5
57.5°	57.1
60°	47.1
62.5°	38.5
65°	32.3
67.5°	26.1
70°	21.1
72.5°	16.1
75°	12.4
77.5°	8.7
80°	5.0
82.5°	2.5
85°	1.2
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)