

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640798

Luminaire Tested: ML5612LSFL4097FS1E - 693SNB - 1200LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640798
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-42)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 693SNB - 1200LM - 3500K
Description: ML56 RR, 40D TIR OPTIC, 6" SATIN NICKLE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1588.0 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.7
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640798
CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 1200LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P640798
 CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 1200LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94																			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82																			
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76																			
5	93	85	80	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72																			
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67																			
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63																			
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60																			
9	77	68	62	58	76	67	62	58	67	62	58	66	61	58	65	61	58	56																			
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142620
5°	138174
10°	120333
15°	98990
20°	77234
25°	58788
30°	42785
35°	29346
40°	18986
45°	11691
50°	6311
55°	2399
60°	1535
65°	545
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11691 cd/sqm



TEST NUMBER: P640798

CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 1200LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.1	14.4
10°-20°	481.9	30.3
20°-30°	445.7	28.1
30°-40°	277.9	17.5
40°-50°	121.4	7.6
50°-60°	27.9	1.8
60°-70°	5.1	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1155.7	72.8
0°-40°	1433.6	90.3
0°-60°	1582.9	99.7
0°-90°	1588.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1588.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2602	
5°	2511	228
15°	1744	482
25°	972	446
35°	438	278
45°	151	121
55°	25	28
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640798

CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 1200LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2601.6
2.5°	2583.5
5°	2510.9
7.5°	2360.0
10°	2161.7
12.5°	1953.7
15°	1744.2
17.5°	1530.5
20°	1323.9
22.5°	1136.7
25°	971.9
27.5°	818.3
30°	675.9
32.5°	548.8
35°	438.5
37.5°	343.5
40°	265.3
42.5°	205.3
45°	150.8
47.5°	111.7
50°	74.0
52.5°	37.7
55°	25.1
57.5°	19.6
60°	14.0
62.5°	8.4
65°	4.2
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)