

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641446

Luminaire Tested: ML5612LSVWFL7597FS1E - 692SC - 600LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641446
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-83)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 692SC - 600LM - 2700K
Description: ML56 RR, 75D TIR OPTIC, 6" SPECULAR CLEAR TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 930.4 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.01
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641446
CATALOG NUMBER: ML5612LSVWFL7597FS1E - 692SC - 600LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P641446

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 692SC - 600LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																												
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85																												
3	101	94	88	84	99	92	87	83	89	85	82	87	83	80	85	82	79	78																												
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71																												
5	89	80	74	69	88	79	73	69	77	72	68	76	71	67	74	70	67	65																												
6	84	74	68	63	83	74	67	63	72	66	62	70	66	62	69	65	61	60																												
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55																												
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51																												
9	71	60	54	50	70	60	54	49	59	53	49	58	53	49	57	52	49	47																												
10	67	57	50	46	66	56	50	46	55	50	46	54	49	46	54	49	46	44																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44350
5°	41008
10°	39350
15°	40363
20°	39653
25°	36637
30°	32473
35°	26020
40°	17833
45°	10288
50°	5586
55°	3336
60°	1776
65°	441
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10288 cd/sqm



TEST NUMBER: P641446

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 692SC - 600LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.9	7.5
10°-20°	199.2	21.4
20°-30°	276.6	29.7
30°-40°	239.1	25.7
40°-50°	108.1	11.6
50°-60°	32.6	3.5
60°-70°	4.9	0.5
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	545.7	58.7
0°-40°	784.8	84.4
0°-60°	925.5	99.5
0°-90°	930.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	930.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	809	
5°	745	70
15°	711	199
25°	606	277
35°	389	239
45°	133	108
55°	35	33
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P641446

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 692SC - 600LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	809.0
2.5°	785.2
5°	745.2
7.5°	715.4
10°	706.9
12.5°	709.5
15°	711.2
17.5°	701.0
20°	679.7
22.5°	645.7
25°	605.7
27.5°	562.3
30°	513.0
32.5°	454.3
35°	388.8
37.5°	319.0
40°	249.2
42.5°	184.6
45°	132.7
47.5°	93.6
50°	65.5
52.5°	46.8
55°	34.9
57.5°	24.7
60°	16.2
62.5°	7.7
65°	3.4
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)