

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641472

Luminaire Tested: ML5612LSVWFL7597FS1E - 693BB - 1200LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641472
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-87)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 693BB - 1200LM - 3000K
Description: ML56 RR, 75D TIR OPTIC, 6" BLACK BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1427.8 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641472

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693BB - 1200LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P641472

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693BB - 1200LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92			92																
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84																
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			77																
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71			71																
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	73	69	66	65			65																
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59																
7	79	69	62	57	78	68	62	57	67	61	57	65	60	56	64	60	56	55			55																
8	75	64	57	53	73	63	57	53	62	56	52	61	56	52	60	55	52	50			50																
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47			47																
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43			43																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54749
5°	55629
10°	57408
15°	59609
20°	60240
25°	57118
30°	51090
35°	41010
40°	27909
45°	16118
50°	8810
55°	5324
60°	2686
65°	700
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16118 cd/sqm



TEST NUMBER: P641472

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693BB - 1200LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.2	6.8
10°-20°	295.8	20.7
20°-30°	430.1	30.1
30°-40°	375.8	26.3
40°-50°	169.4	11.9
50°-60°	51.8	3.6
60°-70°	7.6	0.5
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	823.1	57.7
0°-40°	1199.0	84.0
0°-60°	1420.2	99.5
0°-90°	1427.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1427.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	999	
5°	1011	97
15°	1050	296
25°	944	430
35°	613	376
45°	208	169
55°	56	52
65°	5	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P641472

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693BB - 1200LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	998.7
2.5°	1002.8
5°	1010.9
7.5°	1021.8
10°	1031.3
12.5°	1042.2
15°	1050.3
17.5°	1049.0
20°	1032.6
22.5°	996.0
25°	944.3
27.5°	883.2
30°	807.1
32.5°	714.7
35°	612.8
37.5°	500.0
40°	390.0
42.5°	289.4
45°	207.9
47.5°	146.7
50°	103.3
52.5°	74.7
55°	55.7
57.5°	39.4
60°	24.5
62.5°	12.2
65°	5.4
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)