

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640803

Luminaire Tested: ML5612LSFL4097FS1E - 693SNB - 600LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P640803  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-42)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSFL4097FS1E - 693SNB - 600LM - 3500K  
Description: ML56 RR, 40D TIR OPTIC, 6" SATIN NICKLE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1022.5 lumens  
Efficiency: N/A  
Efficacy: 99.3 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.7  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P640803  
CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 600LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P640803

CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 600LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94				94															
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88															
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82				82															
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76				76															
5	93	85	80	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72				72															
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67				67															
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63				63															
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60				60															
9	77	68	62	58	76	67	62	58	67	62	58	66	61	58	65	61	58	56				56															
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	53				53															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	91829
5°	88966
10°	77481
15°	63735
20°	49728
25°	37853
30°	27549
35°	18892
40°	12223
45°	7528
50°	4068
55°	1548
60°	987
65°	350
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7528 cd/sqm



TEST NUMBER: P640803

CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 600LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	146.9	14.4
10°-20°	310.3	30.3
20°-30°	287.0	28.1
30°-40°	178.9	17.5
40°-50°	78.2	7.6
50°-60°	18.0	1.8
60°-70°	3.3	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	744.1	72.8
0°-40°	923.1	90.3
0°-60°	1019.2	99.7
0°-90°	1022.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1022.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1675	
5°	1617	147
15°	1123	310
25°	626	287
35°	282	179
45°	97	78
55°	16	18
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640803

CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 600LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1675.1
2.5°	1663.4
5°	1616.7
7.5°	1519.6
10°	1391.9
12.5°	1257.9
15°	1123.0
17.5°	985.5
20°	852.4
22.5°	731.9
25°	625.8
27.5°	526.9
30°	435.2
32.5°	353.4
35°	282.3
37.5°	221.2
40°	170.8
42.5°	132.2
45°	97.1
47.5°	71.9
50°	47.7
52.5°	24.3
55°	16.2
57.5°	12.6
60°	9.0
62.5°	5.4
65°	2.7
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)