

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641516

Luminaire Tested: ML5612LSVWFL7597FS1E - 693WB - 1200LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641516
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-86)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 693WB - 1200LM - 2700K
Description: ML56 RR, 75D TIR OPTIC, 6" WHITE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1435.7 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641516

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693WB - 1200LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P641516

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693WB - 1200LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 | 92 | 92 | 92 |
| 2 | 106 | 101 | 96 | 92 | 104 | 99 | 95 | 91 | 96 | 92 | 89 | 93 | 90 | 87 | 90 | 88 | 86 | 84 | 84 | 84 | 84 |
| 3 | 100 | 93 | 87 | 83 | 98 | 91 | 86 | 82 | 89 | 84 | 81 | 86 | 82 | 79 | 84 | 81 | 78 | 76 | 76 | 76 | 76 |
| 4 | 94 | 85 | 79 | 74 | 92 | 84 | 78 | 74 | 82 | 77 | 73 | 80 | 76 | 72 | 78 | 74 | 71 | 70 | 70 | 70 | 70 |
| 5 | 88 | 79 | 72 | 67 | 87 | 78 | 72 | 67 | 76 | 71 | 67 | 74 | 70 | 66 | 73 | 69 | 65 | 64 | 64 | 64 | 64 |
| 6 | 83 | 73 | 66 | 62 | 82 | 72 | 66 | 61 | 71 | 65 | 61 | 69 | 64 | 60 | 68 | 63 | 60 | 58 | 58 | 58 | 58 |
| 7 | 78 | 68 | 61 | 56 | 77 | 67 | 61 | 56 | 66 | 60 | 56 | 65 | 59 | 56 | 63 | 59 | 55 | 54 | 54 | 54 | 54 |
| 8 | 74 | 63 | 57 | 52 | 73 | 63 | 56 | 52 | 61 | 56 | 52 | 60 | 55 | 51 | 59 | 55 | 51 | 50 | 50 | 50 | 50 |
| 9 | 70 | 59 | 52 | 48 | 69 | 59 | 52 | 48 | 58 | 52 | 48 | 57 | 51 | 48 | 56 | 51 | 47 | 46 | 46 | 46 | 46 |
| 10 | 66 | 55 | 49 | 45 | 65 | 55 | 49 | 44 | 54 | 48 | 44 | 53 | 48 | 44 | 52 | 48 | 44 | 43 | 43 | 43 | 43 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 53949 |
| 5° | 54881 |
| 10° | 56623 |
| 15° | 58701 |
| 20° | 59342 |
| 25° | 56253 |
| 30° | 50337 |
| 35° | 40401 |
| 40° | 27795 |
| 45° | 16389 |
| 50° | 9467 |
| 55° | 5935 |
| 60° | 3618 |
| 65° | 1712 |
| 70° | 1058 |
| 75° | 1123 |
| 80° | 1263 |
| 85° | 818 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16389 cd/sqm



TEST NUMBER: P641516

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693WB - 1200LM - 2700K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 95.8 | 6.7 |
| 10°-20° | 291.5 | 20.3 |
| 20°-30° | 423.6 | 29.5 |
| 30°-40° | 371.5 | 25.9 |
| 40°-50° | 172.3 | 12.0 |
| 50°-60° | 58.5 | 4.1 |
| 60°-70° | 14.6 | 1.0 |
| 70°-80° | 5.9 | 0.4 |
| 80°-90° | 2.0 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 810.9 | 56.5 |
| 0°-40° | 1182.4 | 82.4 |
| 0°-60° | 1413.2 | 98.4 |
| 0°-90° | 1435.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1435.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 984 | |
| 5° | 997 | 96 |
| 15° | 1034 | 292 |
| 25° | 930 | 424 |
| 35° | 604 | 371 |
| 45° | 211 | 172 |
| 55° | 62 | 58 |
| 65° | 13 | 15 |
| 75° | 5 | 6 |
| 85° | 1 | 2 |
| 90° | 0 | |



TEST NUMBER: P641516

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693WB - 1200LM - 2700K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 984.1 |
| 2.5° | 988.1 |
| 5° | 997.3 |
| 7.5° | 1006.6 |
| 10° | 1017.2 |
| 12.5° | 1026.4 |
| 15° | 1034.3 |
| 17.5° | 1034.3 |
| 20° | 1017.2 |
| 22.5° | 981.5 |
| 25° | 930.0 |
| 27.5° | 869.2 |
| 30° | 795.2 |
| 32.5° | 706.7 |
| 35° | 603.7 |
| 37.5° | 495.4 |
| 40° | 388.4 |
| 42.5° | 290.6 |
| 45° | 211.4 |
| 47.5° | 153.2 |
| 50° | 111.0 |
| 52.5° | 81.9 |
| 55° | 62.1 |
| 57.5° | 47.6 |
| 60° | 33.0 |
| 62.5° | 18.5 |
| 65° | 13.2 |
| 67.5° | 7.9 |
| 70° | 6.6 |
| 72.5° | 6.6 |
| 75° | 5.3 |
| 77.5° | 5.3 |
| 80° | 4.0 |
| 82.5° | 2.6 |
| 85° | 1.3 |
| 87.5° | 1.3 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)