

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641522

Luminaire Tested: ML5612LSVWFL7597FS1E - 693WB - 600LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641522  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-86)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL7597FS1E - 693WB - 600LM - 3000K  
Description: ML56 RR, 75D TIR OPTIC, 6" WHITE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 950.8 lumens  
Efficiency: N/A  
Efficacy: 92.3 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641522  
CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693WB - 600LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641522

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693WB - 600LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70	70	70	70
5	88	79	72	67	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50	50	50	50
9	70	59	52	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46	46
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	48	44	43	43	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	35732
5°	36347
10°	37497
15°	38877
20°	39297
25°	37254
30°	33341
35°	26756
40°	18406
45°	10854
50°	6268
55°	3928
60°	2401
65°	1129
70°	705
75°	741
80°	821
85°	566

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10854 cd/sqm



TEST NUMBER: P641522

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693WB - 600LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.4	6.7
10°-20°	193.1	20.3
20°-30°	280.6	29.5
30°-40°	246.0	25.9
40°-50°	114.1	12.0
50°-60°	38.7	4.1
60°-70°	9.6	1.0
70°-80°	3.9	0.4
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	537.1	56.5
0°-40°	783.1	82.4
0°-60°	935.9	98.4
0°-90°	950.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	950.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	652	
5°	660	63
15°	685	193
25°	616	281
35°	400	246
45°	140	114
55°	41	39
65°	9	10
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P641522

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 693WB - 600LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	651.8
2.5°	654.4
5°	660.5
7.5°	666.6
10°	673.6
12.5°	679.8
15°	685.0
17.5°	685.0
20°	673.6
22.5°	650.0
25°	615.9
27.5°	575.7
30°	526.7
32.5°	468.0
35°	399.8
37.5°	328.1
40°	257.2
42.5°	192.5
45°	140.0
47.5°	101.5
50°	73.5
52.5°	54.2
55°	41.1
57.5°	31.5
60°	21.9
62.5°	12.2
65°	8.7
67.5°	5.2
70°	4.4
72.5°	4.4
75°	3.5
77.5°	3.5
80°	2.6
82.5°	1.7
85°	0.9
87.5°	0.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)