

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640867

Luminaire Tested: ML5612LSFL4097FS1E - 694WB - 900LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P640867  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-44)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSFL4097FS1E - 694WB - 900LM - 3000K  
Description: ML56 RR, 40D TIR OPTIC, 6" WHITE GIMBAL TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1291.6 lumens  
Efficiency: N/A  
Efficacy: 97.1 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P640867

CATALOG NUMBER: ML5612LSFL4097FS1E - 694WB - 900LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P640867

CATALOG NUMBER: ML5612LSFL4097FS1E - 694WB - 900LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81																			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71																			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	55	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	114821
5°	111121
10°	96719
15°	79439
20°	62008
25°	47047
30°	33822
35°	22988
40°	14778
45°	9575
50°	5552
55°	3116
60°	2094
65°	1453
70°	1074
75°	953
80°	347
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9575 cd/sqm



TEST NUMBER: P640867

CATALOG NUMBER: ML5612LSFL4097FS1E - 694WB - 900LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.5	14.2
10°-20°	387.1	30.0
20°-30°	356.3	27.6
30°-40°	218.1	16.9
40°-50°	97.6	7.6
50°-60°	32.2	2.5
60°-70°	12.0	0.9
70°-80°	4.3	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	926.9	71.8
0°-40°	1145.1	88.7
0°-60°	1274.9	98.7
0°-90°	1291.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1291.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2094	
5°	2019	184
15°	1400	387
25°	778	356
35°	344	218
45°	124	98
55°	33	32
65°	11	12
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P640867

CATALOG NUMBER: ML5612LSFL4097FS1E - 694WB - 900LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2094.5
2.5°	2081.0
5°	2019.3
7.5°	1898.0
10°	1737.5
12.5°	1571.4
15°	1399.7
17.5°	1229.1
20°	1062.9
22.5°	912.5
25°	777.8
27.5°	652.1
30°	534.3
32.5°	431.0
35°	343.5
37.5°	269.4
40°	206.5
42.5°	161.6
45°	123.5
47.5°	90.9
50°	65.1
52.5°	46.0
55°	32.6
57.5°	24.7
60°	19.1
62.5°	15.7
65°	11.2
67.5°	9.0
70°	6.7
72.5°	5.6
75°	4.5
77.5°	2.2
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)