

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641597

Luminaire Tested: ML5612LSVWFL97FS1E - 592H - 600LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641597
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-95)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 592H - 600LM - 3000K
Description: ML56 RR, MILKY OPTIC, 5" HAZE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 857.5 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.97
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641597

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592H - 600LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P641597

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592H - 600LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92																
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84																
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			77																
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71			71																
5	89	80	73	68	87	79	73	68	77	72	68	75	71	67	74	70	66	65			65																
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	64	61	60			60																
7	79	69	62	58	78	68	62	57	67	61	57	66	61	57	64	60	56	55			55																
8	75	64	58	53	73	64	57	53	63	57	53	61	56	53	60	56	52	51			51																
9	71	60	54	49	70	60	53	49	59	53	49	58	53	49	57	52	49	47			47																
10	67	56	50	46	66	56	50	46	55	50	46	54	49	46	54	49	45	44			44																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63176
5°	61825
10°	58195
15°	53400
20°	48791
25°	44492
30°	39943
35°	33797
40°	24701
45°	15429
50°	8805
55°	4817
60°	2479
65°	1139
70°	600
75°	275
80°	409
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15429 cd/sqm



TEST NUMBER: P641597

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592H - 600LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.7	8.5
10°-20°	183.1	21.4
20°-30°	234.3	27.3
30°-40°	214.8	25.0
40°-50°	110.5	12.9
50°-60°	33.7	3.9
60°-70°	7.0	0.8
70°-80°	1.4	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	490.1	57.2
0°-40°	704.9	82.2
0°-60°	849.1	99.0
0°-90°	857.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	857.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	800	
5°	780	73
15°	653	183
25°	511	234
35°	351	215
45°	138	110
55°	35	34
65°	6	7
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P641597

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592H - 600LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	800.3
2.5°	795.1
5°	780.2
7.5°	756.6
10°	726.0
12.5°	690.1
15°	653.4
17.5°	616.7
20°	580.8
22.5°	545.8
25°	510.8
27.5°	475.0
30°	438.2
32.5°	397.1
35°	350.7
37.5°	296.5
40°	239.7
42.5°	185.4
45°	138.2
47.5°	100.6
50°	71.7
52.5°	49.9
55°	35.0
57.5°	23.6
60°	15.7
62.5°	9.6
65°	6.1
67.5°	3.5
70°	2.6
72.5°	1.7
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)