

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641608

Luminaire Tested: ML5612LSVWFL97FS1E - 592SC - 1200LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641608
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-94)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 592SC - 1200LM - 3500K
Description: ML56 RR, MILKY OPTIC, 5" SPECULAR CLEAR TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1410.8 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.95
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641608
CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 1200LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P641608

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 1200LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	79	78			78																
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71			71																
5	90	81	74	69	88	80	74	69	78	73	69	76	71	68	74	70	67	66			66																
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61			61																
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	65	61	58	56			56																
8	76	65	59	54	74	65	59	54	64	58	54	63	57	54	62	57	54	52			52																
9	72	61	55	51	70	61	55	50	60	54	50	59	54	50	58	53	50	48			48																
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108386
5°	109244
10°	105136
15°	93854
20°	82050
25°	72312
30°	63853
35°	54188
40°	39973
45°	24773
50°	13362
55°	6716
60°	3079
65°	1308
70°	646
75°	427
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24773 cd/sqm



TEST NUMBER: P641608

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 1200LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.5	9.2
10°-20°	320.4	22.7
20°-30°	381.7	27.1
30°-40°	344.6	24.4
40°-50°	177.2	12.6
50°-60°	48.1	3.4
60°-70°	7.9	0.6
70°-80°	1.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	831.6	58.9
0°-40°	1176.2	83.4
0°-60°	1401.5	99.3
0°-90°	1410.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1410.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1373	
5°	1379	129
15°	1148	320
25°	830	382
35°	562	345
45°	222	177
55°	49	48
65°	7	8
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P641608

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 1200LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1373.0
2.5°	1375.8
5°	1378.6
7.5°	1360.4
10°	1311.6
12.5°	1237.7
15°	1148.4
17.5°	1060.4
20°	976.7
22.5°	898.6
25°	830.2
27.5°	763.2
30°	700.5
32.5°	633.5
35°	562.3
37.5°	478.6
40°	387.9
42.5°	301.4
45°	221.9
47.5°	159.1
50°	108.8
52.5°	72.6
55°	48.8
57.5°	32.1
60°	19.5
62.5°	11.2
65°	7.0
67.5°	2.8
70°	2.8
72.5°	1.4
75°	1.4
77.5°	1.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)