

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640981

Luminaire Tested: ML5612LSNFL2597FS1E - 593TBZB - 600LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640981
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSNFL2597FS1E - 593TBZB - 600LM - 2700K
Description: ML56 RR, 25D TIR OPTIC, 5" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 828.9 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640981

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593TBZB - 600LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P640981

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593TBZB - 600LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	104	102	101	100	99	98	97	96	94																			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89																			
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83																			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78																			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74																			
6	91	82	77	73	89	82	77	73	80	76	72	79	75	72	78	74	71	70																			
7	87	78	73	69	86	78	72	69	76	72	68	75	71	68	74	71	68	66																			
8	83	75	69	65	82	74	69	65	73	68	65	72	68	65	71	67	64	63																			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60																			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181248
5°	166639
10°	121793
15°	69941
20°	41878
25°	33935
30°	27765
35°	22377
40°	17096
45°	9590
50°	2505
55°	1294
60°	805
65°	318
70°	208
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9590 cd/sqm



TEST NUMBER: P640981

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593TBZB - 600LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.6	21.9
10°-20°	244.5	29.5
20°-30°	179.4	21.6
30°-40°	145.2	17.5
40°-50°	66.2	8.0
50°-60°	9.5	1.1
60°-70°	2.2	0.3
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	605.5	73.0
0°-40°	750.7	90.6
0°-60°	826.4	99.7
0°-90°	828.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	828.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2296	
5°	2103	182
15°	856	245
25°	390	179
35°	232	145
45°	86	66
55°	9	9
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640981

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593TBZB - 600LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2296.0
2.5°	2252.7
5°	2102.9
7.5°	1841.8
10°	1519.4
12.5°	1174.0
15°	855.8
17.5°	626.1
20°	498.5
22.5°	435.6
25°	389.6
27.5°	345.4
30°	304.6
32.5°	267.1
35°	232.2
37.5°	200.8
40°	165.9
42.5°	123.4
45°	85.9
47.5°	47.6
50°	20.4
52.5°	12.8
55°	9.4
57.5°	7.7
60°	5.1
62.5°	3.4
65°	1.7
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)