

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641610

Luminaire Tested: ML5612LSVWFL97FS1E - 592SC - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641610
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-94)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 592SC - 1200LM - 5000K
Description: ML56 RR, MILKY OPTIC, 5" SPECULAR CLEAR TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1518.5 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.95
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641610
CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P641610

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	79	78																			
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71																			
5	90	81	74	69	88	80	74	69	78	73	69	76	71	68	74	70	67	66																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61																			
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	65	61	58	56																			
8	76	65	59	54	74	65	59	54	64	58	54	63	57	54	62	57	54	52																			
9	72	61	55	51	70	61	55	50	60	54	50	59	54	50	58	53	50	48																			
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116667
5°	117588
10°	113168
15°	101021
20°	88317
25°	77834
30°	68720
35°	58332
40°	43023
45°	26659
50°	14381
55°	7239
60°	3316
65°	1401
70°	692
75°	458
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26659 cd/sqm



TEST NUMBER: P641610

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.4	9.2
10°-20°	344.8	22.7
20°-30°	410.8	27.1
30°-40°	370.9	24.4
40°-50°	190.7	12.6
50°-60°	51.7	3.4
60°-70°	8.4	0.6
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	895.1	58.9
0°-40°	1266.0	83.4
0°-60°	1508.5	99.3
0°-90°	1518.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1518.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1478	
5°	1484	139
15°	1236	345
25°	894	411
35°	605	371
45°	239	191
55°	53	52
65°	8	8
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P641610

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1477.9
2.5°	1480.9
5°	1483.9
7.5°	1464.3
10°	1411.8
12.5°	1332.2
15°	1236.1
17.5°	1141.4
20°	1051.3
22.5°	967.2
25°	893.6
27.5°	821.5
30°	753.9
32.5°	681.9
35°	605.3
37.5°	515.1
40°	417.5
42.5°	324.4
45°	238.8
47.5°	171.2
50°	117.1
52.5°	78.1
55°	52.6
57.5°	34.5
60°	21.0
62.5°	12.0
65°	7.5
67.5°	3.0
70°	3.0
72.5°	1.5
75°	1.5
77.5°	1.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)