

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640990

Luminaire Tested: ML5612LSNFL2597FS1E - 593TBZB - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640990
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSNFL2597FS1E - 593TBZB - 900LM - 5000K
Description: ML56 RR, 25D TIR OPTIC, 5" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1209.4 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640990

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593TBZB - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P640990

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593TBZB - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94																												
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89																												
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83																												
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78																												
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74																												
6	91	82	77	73	89	82	77	73	80	76	72	79	75	72	78	74	71	70																												
7	87	78	73	69	86	78	72	69	76	72	68	75	71	68	74	71	68	66																												
8	83	75	69	65	82	74	69	65	73	68	65	72	68	65	71	67	64	63																												
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60																												
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	264460
5°	243140
10°	177696
15°	102051
20°	61107
25°	49517
30°	40508
35°	32659
40°	24938
45°	14000
50°	3660
55°	1886
60°	1168
65°	467
70°	277
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14000 cd/sqm



TEST NUMBER: P640990

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593TBZB - 900LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	265.0	21.9
10°-20°	356.8	29.5
20°-30°	261.7	21.6
30°-40°	211.9	17.5
40°-50°	96.6	8.0
50°-60°	13.8	1.1
60°-70°	3.2	0.3
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	883.5	73.1
0°-40°	1095.3	90.6
0°-60°	1205.7	99.7
0°-90°	1209.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1209.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3350	
5°	3068	265
15°	1249	357
25°	568	262
35°	339	212
45°	125	97
55°	14	14
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640990

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593TBZB - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3350.1
2.5°	3286.8
5°	3068.3
7.5°	2687.3
10°	2216.8
12.5°	1712.9
15°	1248.7
17.5°	913.5
20°	727.4
22.5°	635.5
25°	568.5
27.5°	503.9
30°	444.4
32.5°	389.7
35°	338.9
37.5°	292.9
40°	242.0
42.5°	180.0
45°	125.4
47.5°	69.5
50°	29.8
52.5°	18.6
55°	13.7
57.5°	11.2
60°	7.4
62.5°	5.0
65°	2.5
67.5°	1.2
70°	1.2
72.5°	1.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)