

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641616

Luminaire Tested: ML5612LSVWFL97FS1E - 592SC - 900LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641616
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-94)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 592SC - 900LM - 2700K
Description: ML56 RR, MILKY OPTIC, 5" SPECULAR CLEAR TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1103.1 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.95
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641616
CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 900LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P641616

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 900LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	79	78																			
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71																			
5	90	81	74	69	88	80	74	69	78	73	69	76	71	68	74	70	67	66																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61																			
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	65	61	58	56																			
8	76	65	59	54	74	65	59	54	64	58	54	63	57	54	62	57	54	52																			
9	72	61	55	51	70	61	55	50	60	54	50	59	54	50	58	53	50	48																			
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84743
5°	85408
10°	82203
15°	73373
20°	64148
25°	56538
30°	49915
35°	42364
40°	31255
45°	19369
50°	10451
55°	5257
60°	2416
65°	1027
70°	508
75°	336
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19369 cd/sqm



TEST NUMBER: P641616

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 900LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.2	9.2
10°-20°	250.5	22.7
20°-30°	298.4	27.1
30°-40°	269.4	24.4
40°-50°	138.6	12.6
50°-60°	37.6	3.4
60°-70°	6.2	0.6
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	650.1	58.9
0°-40°	919.6	83.4
0°-60°	1095.7	99.3
0°-90°	1103.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1103.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1074	
5°	1078	101
15°	898	250
25°	649	298
35°	440	269
45°	174	139
55°	38	38
65°	6	6
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P641616

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592SC - 900LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1073.5
2.5°	1075.6
5°	1077.8
7.5°	1063.6
10°	1025.5
12.5°	967.6
15°	897.8
17.5°	829.1
20°	763.6
22.5°	702.6
25°	649.1
27.5°	596.7
30°	547.6
32.5°	495.3
35°	439.6
37.5°	374.2
40°	303.3
42.5°	235.6
45°	173.5
47.5°	124.4
50°	85.1
52.5°	56.7
55°	38.2
57.5°	25.1
60°	15.3
62.5°	8.7
65°	5.5
67.5°	2.2
70°	2.2
72.5°	1.1
75°	1.1
77.5°	1.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)