

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641627

Luminaire Tested: ML5612LSVWFL97FS1E - 592W - 600LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641627
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-96)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 592W - 600LM - 3000K
Description: ML56 RR, MILKY OPTIC, 5" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 852.7 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641627
CATALOG NUMBER: ML5612LSVWFL97FS1E - 592W - 600LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P641627

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592W - 600LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78																			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	70																			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62																			
5	84	73	65	60	82	72	65	59	70	64	59	68	62	58	66	61	58	56																			
6	78	67	59	54	76	66	59	53	64	58	53	63	57	53	61	56	52	50																			
7	73	61	54	49	72	61	54	48	59	53	48	58	52	48	57	52	48	46																			
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42																			
9	65	53	45	41	63	52	45	41	51	45	40	50	44	40	49	44	40	38																			
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27662
5°	27575
10°	27260
15°	26799
20°	26270
25°	25707
30°	24687
35°	22299
40°	17769
45°	12606
50°	9177
55°	7101
60°	6140
65°	5669
70°	5321
75°	4999
80°	4420
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12606 cd/sqm



TEST NUMBER: P641627

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592W - 600LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	5.6
10°-20°	133.1	15.6
20°-30°	194.9	22.9
30°-40°	204.3	24.0
40°-50°	129.1	15.1
50°-60°	69.1	8.1
60°-70°	43.5	5.1
70°-80°	24.9	2.9
80°-90°	6.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	375.5	44.0
0°-40°	579.7	68.0
0°-60°	777.9	91.2
0°-90°	852.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	852.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	505	
5°	501	47
15°	472	133
25°	425	195
35°	333	204
45°	163	129
55°	74	69
65°	44	43
75°	24	25
85°	5	6
90°	0	



TEST NUMBER: P641627

CATALOG NUMBER: ML5612LSVWFL97FS1E - 592W - 600LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	504.6
2.5°	503.7
5°	501.1
7.5°	495.8
10°	489.7
12.5°	481.8
15°	472.2
17.5°	461.7
20°	450.3
22.5°	437.2
25°	425.0
27.5°	409.2
30°	390.0
32.5°	365.5
35°	333.2
37.5°	293.8
40°	248.3
42.5°	202.9
45°	162.6
47.5°	131.2
50°	107.6
52.5°	89.2
55°	74.3
57.5°	64.7
60°	56.0
62.5°	49.0
65°	43.7
67.5°	38.5
70°	33.2
72.5°	28.9
75°	23.6
77.5°	18.4
80°	14.0
82.5°	9.6
85°	5.2
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)