

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641679

Luminaire Tested: ML5612LSVWFL97FS1E - 593TBZB - 900LM - 4000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641679  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-100)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL97FS1E - 593TBZB - 900LM - 4000K  
Description: ML56 RR, MILKY OPTIC, 5" TUSCON BRONZE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 910.3 lumens  
Efficiency: N/A  
Efficacy: 68.4 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.12  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641679  
CATALOG NUMBER: ML5612LSVWFL97FS1E - 593TBZB - 900LM - 4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641679

CATALOG NUMBER: ML5612LSVWFL97FS1E - 593TBZB - 900LM - 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				
2	106	101	96	92	104	99	95	91	96	92	89	92	90	87	90	87	85	84				
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				
4	94	85	79	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63				
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	62	59	57				
7	78	67	60	55	76	66	60	55	65	59	55	64	58	54	62	58	54	53				
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48				
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45				
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	50838
5°	50636
10°	50027
15°	49289
20°	48371
25°	47227
30°	44902
35°	39579
40°	29668
45°	18420
50°	10513
55°	5629
60°	2747
65°	1158
70°	577
75°	366
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18420 cd/sqm



TEST NUMBER: P641679

CATALOG NUMBER: ML5612LSVWFL97FS1E - 593TBZB - 900LM - 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.5	6.6
10°-20°	169.9	18.7
20°-30°	248.4	27.3
30°-40°	250.7	27.5
40°-50°	132.3	14.5
50°-60°	39.6	4.4
60°-70°	7.6	0.8
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	478.8	52.6
0°-40°	729.6	80.1
0°-60°	901.5	99.0
0°-90°	910.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	910.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	644	
5°	639	61
15°	603	170
25°	542	248
35°	411	251
45°	165	132
55°	41	40
65°	6	8
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P641679

CATALOG NUMBER: ML5612LSVWFL97FS1E - 593TBZB - 900LM - 4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	644.0
2.5°	642.8
5°	639.0
7.5°	632.8
10°	624.1
12.5°	614.2
15°	603.1
17.5°	590.6
20°	575.8
22.5°	559.6
25°	542.2
27.5°	519.9
30°	492.6
32.5°	457.9
35°	410.7
37.5°	353.6
40°	287.9
42.5°	222.1
45°	165.0
47.5°	120.4
50°	85.6
52.5°	59.6
55°	40.9
57.5°	27.3
60°	17.4
62.5°	11.2
65°	6.2
67.5°	3.7
70°	2.5
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)