

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641056

Luminaire Tested: ML5612LSNFL2597FS1E - 596WB - 600LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641056
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSNFL2597FS1E - 596WB - 600LM - 2700K
Description: ML56 RR, 25D TIR OPTIC, 5" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 915.9 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.44
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641056
CATALOG NUMBER: ML5612LSNFL2597FS1E - 596WB - 600LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P641056

CATALOG NUMBER: ML5612LSNFL2597FS1E - 596WB - 600LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75																			
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70																			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65																			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62																			
8	80	71	65	61	79	70	64	60	69	64	60	68	63	60	67	63	60	58																			
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181233
5°	164135
10°	119525
15°	68478
20°	42802
25°	34971
30°	28841
35°	23360
40°	18755
45°	14904
50°	10034
55°	4569
60°	2558
65°	2391
70°	1962
75°	1830
80°	1955
85°	2355

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14904 cd/sqm



TEST NUMBER: P641056

CATALOG NUMBER: ML5612LSNFL2597FS1E - 596WB - 600LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.0	19.5
10°-20°	241.2	26.3
20°-30°	184.8	20.2
30°-40°	152.2	16.6
40°-50°	101.9	11.1
50°-60°	35.4	3.9
60°-70°	12.3	1.3
70°-80°	6.7	0.7
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	605.0	66.1
0°-40°	757.3	82.7
0°-60°	894.5	97.7
0°-90°	915.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	915.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2296	
5°	2071	179
15°	838	241
25°	402	185
35°	242	152
45°	134	102
55°	33	35
65°	13	12
75°	6	7
85°	3	2
90°	0	



TEST NUMBER: P641056
CATALOG NUMBER: ML5612LSNFL2597FS1E - 596WB - 600LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2295.8
2.5°	2243.9
5°	2071.3
7.5°	1809.3
10°	1491.1
12.5°	1143.2
15°	837.9
17.5°	626.9
20°	509.5
22.5°	448.3
25°	401.5
27.5°	356.4
30°	316.4
32.5°	278.2
35°	242.4
37.5°	210.1
40°	182.0
42.5°	156.5
45°	133.5
47.5°	109.7
50°	81.7
52.5°	57.8
55°	33.2
57.5°	20.4
60°	16.2
62.5°	14.5
65°	12.8
67.5°	10.2
70°	8.5
72.5°	6.8
75°	6.0
77.5°	6.0
80°	4.3
82.5°	3.4
85°	2.6
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)