

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641716

Luminaire Tested: ML5612LSVWFL97FS1E - 594TBZB - 600LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641716  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-103)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL97FS1E - 594TBZB - 600LM - 2700K  
Description: ML56 RR, MILKY OPTIC, 5" TUSCON BRONZE GIMBAL TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 906.5 lumens  
Efficiency: N/A  
Efficacy: 88.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.27  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641716  
CATALOG NUMBER: ML5612LSVWFL97FS1E - 594TBZB - 600LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P641716

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594TBZB - 600LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	107	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	88	83	99	92	87	82	89	84	80	85	82	78	82	79	76	74			74
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64			64
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56			56
5	79	68	59	53	77	67	59	53	64	58	52	63	57	52	61	55	51	49			49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44			44
7	69	56	48	42	67	55	47	42	54	47	41	52	46	41	51	45	41	39			39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	43	38	34	32			32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			29

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	31963
5°	31879
10°	31775
15°	31562
20°	31158
25°	30599
30°	29698
35°	28525
40°	26731
45°	24695
50°	22143
55°	19309
60°	16388
65°	13654
70°	11379
75°	9852
80°	8501
85°	8514

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24695 cd/sqm



TEST NUMBER: P641716

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594TBZB - 600LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.2	4.2
10°-20°	108.7	12.0
20°-30°	161.5	17.8
30°-40°	184.2	20.3
40°-50°	170.0	18.8
50°-60°	125.6	13.9
60°-70°	73.3	8.1
70°-80°	34.5	3.8
80°-90°	10.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	308.4	34.0
0°-40°	492.6	54.3
0°-60°	788.2	87.0
0°-90°	906.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	906.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	405	
5°	402	38
15°	386	109
25°	351	161
35°	296	184
45°	221	170
55°	140	126
65°	73	73
75°	32	35
85°	9	10
90°	0	



TEST NUMBER: P641716

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594TBZB - 600LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	404.9
2.5°	404.0
5°	402.3
7.5°	399.8
10°	396.4
12.5°	391.3
15°	386.2
17.5°	378.5
20°	370.9
22.5°	361.5
25°	351.3
27.5°	339.4
30°	325.8
32.5°	311.3
35°	296.0
37.5°	278.1
40°	259.4
42.5°	240.7
45°	221.2
47.5°	200.7
50°	180.3
52.5°	159.9
55°	140.3
57.5°	120.8
60°	103.8
62.5°	86.8
65°	73.1
67.5°	60.4
70°	49.3
72.5°	40.0
75°	32.3
77.5°	24.7
80°	18.7
82.5°	13.6
85°	9.4
87.5°	6.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)