

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641113

Luminaire Tested: ML5612LSNFL2597FS1E - 692W - 1200LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641113  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSNFL2597FS1E - 692W - 1200LM - 3500K  
Description: ML56 RR, 25D TIR OPTIC, 6" WHITE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1493.2 lumens  
Efficiency: N/A  
Efficacy: 90.5 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 16.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641113

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692W - 1200LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P641113

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692W - 1200LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66			
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	62			
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	61	57	56			
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	54			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	207187
5°	189093
10°	138703
15°	79495
20°	48998
25°	39831
30°	32942
35°	26890
40°	21562
45°	16761
50°	9279
55°	3603
60°	2905
65°	2529
70°	2244
75°	2372
80°	2210
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16761 cd/sqm



TEST NUMBER: P641113

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692W - 1200LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	297.2	19.9
10°-20°	402.8	27.0
20°-30°	303.7	20.3
30°-40°	251.8	16.9
40°-50°	160.5	10.8
50°-60°	42.7	2.9
60°-70°	19.8	1.3
70°-80°	11.3	0.8
80°-90°	3.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1003.8	67.2
0°-40°	1255.6	84.1
0°-60°	1458.9	97.7
0°-90°	1493.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1493.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3779	
5°	3436	297
15°	1401	403
25°	658	304
35°	402	252
45°	216	161
55°	38	43
65°	20	20
75°	11	11
85°	3	3
90°	0	



TEST NUMBER: P641113

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692W - 1200LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3779.4
2.5°	3701.3
5°	3436.2
7.5°	3009.3
10°	2491.7
12.5°	1916.9
15°	1400.7
17.5°	1045.0
20°	839.9
22.5°	736.6
25°	658.5
27.5°	586.0
30°	520.4
32.5°	459.0
35°	401.8
37.5°	348.8
40°	301.3
42.5°	258.1
45°	216.2
47.5°	160.4
50°	108.8
52.5°	57.2
55°	37.7
57.5°	30.7
60°	26.5
62.5°	23.7
65°	19.5
67.5°	16.7
70°	14.0
72.5°	12.6
75°	11.2
77.5°	8.4
80°	7.0
82.5°	4.2
85°	2.8
87.5°	1.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)