

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641732

Luminaire Tested: ML5612LSVWFL97FS1E - 594WB - 600LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641732  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-101)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL97FS1E - 594WB - 600LM - 3000K  
Description: ML56 RR, MILKY OPTIC, 5" WHITE GIMBAL TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 959.5 lumens  
Efficiency: N/A  
Efficacy: 93.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.28  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641732  
CATALOG NUMBER: ML5612LSVWFL97FS1E - 594WB - 600LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641732

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594WB - 600LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	94	88	82	99	92	86	82	88	84	80	85	81	78	82	79	76	74																			
3	93	83	76	70	91	82	75	69	79	73	68	76	71	67	74	70	66	64																			
4	86	75	67	60	84	73	66	60	71	64	59	69	63	58	67	62	58	56																			
5	79	67	59	53	77	66	58	53	64	57	52	62	56	51	60	55	51	49																			
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43																			
7	68	56	47	42	67	55	47	41	53	46	41	52	46	41	51	45	41	39																			
8	64	51	43	37	62	50	43	37	49	42	37	48	41	37	47	41	37	35																			
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31																			
10	56	43	36	31	55	43	36	31	42	35	31	41	35	31	40	34	30	29																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	33139
5°	33131
10°	33025
15°	32813
20°	32553
25°	31992
30°	31174
35°	30009
40°	28298
45°	26168
50°	23518
55°	20699
60°	17541
65°	14868
70°	12510
75°	10675
80°	9547
85°	8695

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 26168 cd/sqm



TEST NUMBER: P641732

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594WB - 600LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.7	4.1
10°-20°	113.3	11.8
20°-30°	169.0	17.6
30°-40°	193.9	20.2
40°-50°	180.0	18.8
50°-60°	134.5	14.0
60°-70°	79.6	8.3
70°-80°	38.3	4.0
80°-90°	11.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	322.1	33.6
0°-40°	515.9	53.8
0°-60°	830.4	86.5
0°-90°	959.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	959.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	420	
5°	418	40
15°	402	113
25°	367	169
35°	311	194
45°	234	180
55°	150	134
65°	80	80
75°	35	38
85°	10	11
90°	0	



TEST NUMBER: P641732

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594WB - 600LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	419.8
2.5°	419.8
5°	418.1
7.5°	415.4
10°	412.0
12.5°	407.6
15°	401.5
17.5°	395.3
20°	387.5
22.5°	377.8
25°	367.3
27.5°	356.0
30°	342.0
32.5°	327.1
35°	311.4
37.5°	293.0
40°	274.6
42.5°	254.5
45°	234.4
47.5°	212.5
50°	191.5
52.5°	170.6
55°	150.4
57.5°	130.3
60°	111.1
62.5°	94.5
65°	79.6
67.5°	65.6
70°	54.2
72.5°	44.6
75°	35.0
77.5°	28.0
80°	21.0
82.5°	14.9
85°	9.6
87.5°	6.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)