

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641734

Luminaire Tested: ML5612LSVWFL97FS1E - 594WB - 600LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641734
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-101)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 594WB - 600LM - 4000K
Description: ML56 RR, MILKY OPTIC, 5" WHITE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1060.5 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.28
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641734

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594WB - 600LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641734

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594WB - 600LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	94	88	82	99	92	86	82	88	84	80	85	81	78	82	79	76	74																			
3	93	83	76	70	91	82	75	69	79	73	68	76	71	67	74	70	66	64																			
4	86	75	67	60	84	73	66	60	71	64	59	69	63	58	67	62	58	56																			
5	79	67	59	53	77	66	58	53	64	57	52	62	56	51	60	55	51	49																			
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43																			
7	68	56	47	42	67	55	47	41	53	46	41	52	46	41	51	45	41	39																			
8	64	51	43	37	62	50	43	37	49	42	37	48	41	37	47	41	37	35																			
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31																			
10	56	43	36	31	55	43	36	31	42	35	31	41	35	31	40	34	30	29																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36629
5°	36618
10°	36496
15°	36262
20°	35972
25°	35363
30°	34456
35°	33161
40°	31276
45°	28926
50°	25999
55°	22888
60°	19388
65°	16438
70°	13825
75°	11804
80°	10547
85°	9601

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 28926 cd/sqm



TEST NUMBER: P641734

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594WB - 600LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.9	4.1
10°-20°	125.2	11.8
20°-30°	186.8	17.6
30°-40°	214.3	20.2
40°-50°	199.0	18.8
50°-60°	148.6	14.0
60°-70°	88.0	8.3
70°-80°	42.3	4.0
80°-90°	12.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	355.9	33.6
0°-40°	570.2	53.8
0°-60°	917.8	86.5
0°-90°	1060.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1060.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	464	
5°	462	44
15°	444	125
25°	406	187
35°	344	214
45°	259	199
55°	166	149
65°	88	88
75°	39	42
85°	11	12
90°	0	



TEST NUMBER: P641734

CATALOG NUMBER: ML5612LSVWFL97FS1E - 594WB - 600LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	464.0
2.5°	464.0
5°	462.1
7.5°	459.2
10°	455.3
12.5°	450.5
15°	443.7
17.5°	436.9
20°	428.2
22.5°	417.6
25°	406.0
27.5°	393.4
30°	378.0
32.5°	361.5
35°	344.1
37.5°	323.8
40°	303.5
42.5°	281.3
45°	259.1
47.5°	234.9
50°	211.7
52.5°	188.5
55°	166.3
57.5°	144.0
60°	122.8
62.5°	104.4
65°	88.0
67.5°	72.5
70°	59.9
72.5°	49.3
75°	38.7
77.5°	30.9
80°	23.2
82.5°	16.4
85°	10.6
87.5°	6.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)