

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641122

Luminaire Tested: ML5612LSNFL2597FS1E - 692W - 900LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641122  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSNFL2597FS1E - 692W - 900LM - 3000K  
Description: ML56 RR, 25D TIR OPTIC, 6" WHITE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1200.7 lumens  
Efficiency: N/A  
Efficacy: 90.3 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641122

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692W - 900LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641122

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692W - 900LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66			
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	62			
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	61	57	56			
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	54			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	166615
5°	152063
10°	111543
15°	63928
20°	39402
25°	32034
30°	26491
35°	21623
40°	17340
45°	13482
50°	7462
55°	2896
60°	2335
65°	2037
70°	1795
75°	1906
80°	1768
85°	1384

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13482 cd/sqm



TEST NUMBER: P641122

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692W - 900LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	239.0	19.9
10°-20°	323.9	27.0
20°-30°	244.2	20.3
30°-40°	202.5	16.9
40°-50°	129.1	10.8
50°-60°	34.4	2.9
60°-70°	16.0	1.3
70°-80°	9.0	0.8
80°-90°	2.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	807.2	67.2
0°-40°	1009.7	84.1
0°-60°	1173.2	97.7
0°-90°	1200.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1200.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3039	
5°	2763	239
15°	1126	324
25°	530	244
35°	323	202
45°	174	129
55°	30	34
65°	16	16
75°	9	9
85°	2	3
90°	0	



TEST NUMBER: P641122

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692W - 900LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3039.3
2.5°	2976.5
5°	2763.3
7.5°	2420.0
10°	2003.8
12.5°	1541.5
15°	1126.4
17.5°	840.3
20°	675.4
22.5°	592.4
25°	529.6
27.5°	471.2
30°	418.5
32.5°	369.1
35°	323.1
37.5°	280.5
40°	242.3
42.5°	207.6
45°	173.9
47.5°	129.0
50°	87.5
52.5°	46.0
55°	30.3
57.5°	24.7
60°	21.3
62.5°	19.1
65°	15.7
67.5°	13.5
70°	11.2
72.5°	10.1
75°	9.0
77.5°	6.7
80°	5.6
82.5°	3.4
85°	2.2
87.5°	1.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)