

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641745

Luminaire Tested: ML5612LSVWFL97FS1E - 596WB - 1200LM - 5000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641745  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-104)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL97FS1E - 596WB - 1200LM - 5000K  
Description: ML56 RR, MILKY OPTIC, 5" SHALLOW WHITE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1529.0 lumens  
Efficiency: N/A  
Efficacy: 92.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.24  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 16.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641745  
CATALOG NUMBER: ML5612LSVWFL97FS1E - 596WB - 1200LM - 5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641745

CATALOG NUMBER: ML5612LSVWFL97FS1E - 596WB - 1200LM - 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	98	96	97	95	93	94	92	91	89																			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78																			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69																			
4	89	79	71	66	87	77	71	65	75	69	64	73	68	64	71	66	63	61																			
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54																			
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49																			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40																			
9	63	51	44	39	62	50	43	39	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	63287
5°	63291
10°	62941
15°	62324
20°	61544
25°	60414
30°	58976
35°	56424
40°	51206
45°	41731
50°	30604
55°	21897
60°	16357
65°	13187
70°	11425
75°	10980
80°	10910
85°	9510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 41731 cd/sqm



TEST NUMBER: P641745

CATALOG NUMBER: ML5612LSVWFL97FS1E - 596WB - 1200LM - 5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.8	5.0
10°-20°	215.1	14.1
20°-30°	319.5	20.9
30°-40°	362.9	23.7
40°-50°	286.4	18.7
50°-60°	147.4	9.6
60°-70°	71.6	4.7
70°-80°	38.2	2.5
80°-90°	12.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	610.3	39.9
0°-40°	973.2	63.6
0°-60°	1407.0	92.0
0°-90°	1529.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1529.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	802	
5°	799	76
15°	763	215
25°	694	319
35°	586	363
45°	374	286
55°	159	147
65°	71	72
75°	36	38
85°	10	12
90°	0	



TEST NUMBER: P641745

CATALOG NUMBER: ML5612LSVWFL97FS1E - 596WB - 1200LM - 5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	801.7
2.5°	801.7
5°	798.7
7.5°	792.7
10°	785.2
12.5°	774.6
15°	762.6
17.5°	749.1
20°	732.6
22.5°	714.6
25°	693.6
27.5°	672.6
30°	647.0
32.5°	618.5
35°	585.5
37.5°	546.5
40°	496.9
42.5°	438.4
45°	373.8
47.5°	307.8
50°	249.2
52.5°	199.7
55°	159.1
57.5°	127.6
60°	103.6
62.5°	84.1
65°	70.6
67.5°	58.5
70°	49.5
72.5°	42.0
75°	36.0
77.5°	30.0
80°	24.0
82.5°	18.0
85°	10.5
87.5°	4.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)