

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641747

Luminaire Tested: ML5612LSVWFL97FS1E - 596WB - 600LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641747
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-104)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 596WB - 600LM - 3000K
Description: ML56 RR, MILKY OPTIC, 5" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 890.4 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.24
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641747
CATALOG NUMBER: ML5612LSVWFL97FS1E - 596WB - 600LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P641747

CATALOG NUMBER: ML5612LSVWFL97FS1E - 596WB - 600LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	98	96	97	95	93	94	92	91	89																			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78																			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69																			
4	89	79	71	66	87	77	71	65	75	69	64	73	68	64	71	66	63	61																			
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54																			
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49																			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40																			
9	63	51	44	39	62	50	43	39	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36850
5°	36856
10°	36649
15°	36294
20°	35837
25°	35180
30°	34346
35°	32862
40°	29823
45°	24304
50°	17820
55°	12758
60°	9520
65°	7677
70°	6647
75°	6405
80°	6364
85°	5525

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24304 cd/sqm



TEST NUMBER: P641747

CATALOG NUMBER: ML5612LSVWFL97FS1E - 596WB - 600LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	5.0
10°-20°	125.2	14.1
20°-30°	186.0	20.9
30°-40°	211.4	23.7
40°-50°	166.8	18.7
50°-60°	85.8	9.6
60°-70°	41.7	4.7
70°-80°	22.3	2.5
80°-90°	7.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	355.4	39.9
0°-40°	566.7	63.6
0°-60°	819.4	92.0
0°-90°	890.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	890.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	467	
5°	465	44
15°	444	125
25°	404	186
35°	341	211
45°	218	167
55°	93	86
65°	41	42
75°	21	22
85°	6	7
90°	0	



TEST NUMBER: P641747

CATALOG NUMBER: ML5612LSVWFL97FS1E - 596WB - 600LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	466.8
2.5°	466.8
5°	465.1
7.5°	461.6
10°	457.2
12.5°	451.1
15°	444.1
17.5°	436.2
20°	426.6
22.5°	416.1
25°	403.9
27.5°	391.7
30°	376.8
32.5°	360.2
35°	341.0
37.5°	318.2
40°	289.4
42.5°	255.3
45°	217.7
47.5°	179.2
50°	145.1
52.5°	116.3
55°	92.7
57.5°	74.3
60°	60.3
62.5°	49.0
65°	41.1
67.5°	34.1
70°	28.8
72.5°	24.5
75°	21.0
77.5°	17.5
80°	14.0
82.5°	10.5
85°	6.1
87.5°	2.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)