

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641761

Luminaire Tested: ML5612LSVWFL97FS1E - 691WB - 600LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641761  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-105)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL97FS1E - 691WB - 600LM - 2700K  
Description: ML56 RR, MILKY OPTIC, 6" DEADFRONT TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 893.8 lumens  
Efficiency: N/A  
Efficacy: 86.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.28  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641761  
CATALOG NUMBER: ML5612LSVWFL97FS1E - 691WB - 600LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P641761

CATALOG NUMBER: ML5612LSVWFL97FS1E - 691WB - 600LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78																			
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68																			
4	88	78	71	65	86	77	70	64	75	68	64	72	67	63	70	66	62	60																			
5	82	71	63	57	80	70	62	57	68	61	56	66	60	56	64	59	55	53																			
6	76	65	57	51	75	64	56	51	62	55	50	60	54	50	59	54	50	48																			
7	71	59	51	46	70	58	51	46	57	50	45	55	49	45	54	49	45	43																			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	40	39																			
9	62	50	43	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35																			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	24291
5°	24241
10°	24142
15°	23939
20°	23715
25°	23306
30°	22769
35°	21971
40°	20818
45°	18793
50°	14865
55°	10571
60°	7269
65°	5189
70°	3959
75°	3431
80°	3504
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18793 cd/sqm



TEST NUMBER: P641761

CATALOG NUMBER: ML5612LSVWFL97FS1E - 691WB - 600LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.8	4.7
10°-20°	119.0	13.3
20°-30°	177.4	19.8
30°-40°	204.8	22.9
40°-50°	183.4	20.5
50°-60°	101.4	11.3
60°-70°	41.7	4.7
70°-80°	17.7	2.0
80°-90°	6.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.2	37.8
0°-40°	543.0	60.7
0°-60°	827.8	92.6
0°-90°	893.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	893.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	443	
5°	440	42
15°	422	119
25°	385	177
35°	328	205
45°	242	183
55°	111	101
65°	40	42
75°	16	18
85°	6	7
90°	0	



TEST NUMBER: P641761

CATALOG NUMBER: ML5612LSVWFL97FS1E - 691WB - 600LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	443.1
2.5°	442.2
5°	440.5
7.5°	438.0
10°	433.7
12.5°	428.6
15°	421.8
17.5°	414.2
20°	406.5
22.5°	396.3
25°	385.3
27.5°	373.4
30°	359.7
32.5°	345.3
35°	328.3
37.5°	310.4
40°	290.9
42.5°	268.7
45°	242.4
47.5°	210.1
50°	174.3
52.5°	139.5
55°	110.6
57.5°	85.9
60°	66.3
62.5°	51.9
65°	40.0
67.5°	31.5
70°	24.7
72.5°	19.6
75°	16.2
77.5°	13.6
80°	11.1
82.5°	9.4
85°	6.0
87.5°	3.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)