

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641769

Luminaire Tested: ML5612LSVWFL97FS1E - 691WB - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641769
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-105)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 691WB - 900LM - 4000K
Description: ML56 RR, MILKY OPTIC, 6" DEADFRONT TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1303.6 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.28
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641769
CATALOG NUMBER: ML5612LSVWFL97FS1E - 691WB - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641769
 CATALOG NUMBER: ML5612LSVWFL97FS1E - 691WB - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78																			
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68																			
4	88	78	71	65	86	77	70	64	75	68	64	72	67	63	70	66	62	60																			
5	82	71	63	57	80	70	62	57	68	61	56	66	60	56	64	59	55	53																			
6	76	65	57	51	75	64	56	51	62	55	50	60	54	50	59	54	50	48																			
7	71	59	51	46	70	58	51	46	57	50	45	55	49	45	54	49	45	43																			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	40	39																			
9	62	50	43	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35																			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35430
5°	35357
10°	35214
15°	34915
20°	34589
25°	33988
30°	33214
35°	32043
40°	30357
45°	27406
50°	21688
55°	15416
60°	10613
65°	7562
70°	5770
75°	4999
80°	5083
85°	5472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27406 cd/sqm



TEST NUMBER: P641769

CATALOG NUMBER: ML5612LSVWFL97FS1E - 691WB - 900LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.0	4.7
10°-20°	173.5	13.3
20°-30°	258.7	19.8
30°-40°	298.7	22.9
40°-50°	267.5	20.5
50°-60°	147.9	11.3
60°-70°	60.7	4.7
70°-80°	25.8	2.0
80°-90°	9.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	493.2	37.8
0°-40°	791.9	60.7
0°-60°	1207.4	92.6
0°-90°	1303.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1303.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	646	
5°	642	61
15°	615	174
25°	562	259
35°	479	299
45°	354	268
55°	161	148
65°	58	61
75°	24	26
85°	9	10
90°	0	



TEST NUMBER: P641769

CATALOG NUMBER: ML5612LSVWFL97FS1E - 691WB - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	646.3
2.5°	645.0
5°	642.5
7.5°	638.8
10°	632.6
12.5°	625.2
15°	615.2
17.5°	604.1
20°	592.9
22.5°	578.0
25°	561.9
27.5°	544.5
30°	524.7
32.5°	503.6
35°	478.8
37.5°	452.8
40°	424.2
42.5°	392.0
45°	353.5
47.5°	306.4
50°	254.3
52.5°	203.4
55°	161.3
57.5°	125.3
60°	96.8
62.5°	75.7
65°	58.3
67.5°	45.9
70°	36.0
72.5°	28.5
75°	23.6
77.5°	19.8
80°	16.1
82.5°	13.6
85°	8.7
87.5°	5.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)