

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641206

Luminaire Tested: ML5612LSNFL2597FS1E - 694WB - 600LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641206
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSNFL2597FS1E - 694WB - 600LM - 2700K
Description: ML56 RR, 25D TIR OPTIC, 6" WHITE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 931.2 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641206

CATALOG NUMBER: ML5612LSNFL2597FS1E - 694WB - 600LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P641206
 CATALOG NUMBER: ML5612LSNFL2597FS1E - 694WB - 600LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78																			
4	96	88	82	78	94	87	81	77	85	80	76	82	78	75	81	77	74	73																			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																			
6	87	77	71	67	85	76	71	66	75	70	66	74	69	66	72	68	65	64																			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60																			
8	79	69	63	59	77	69	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	66	60	56	74	65	60	56	64	59	55	63	59	55	62	58	55	54																			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125308
5°	114417
10°	83042
15°	47282
20°	28959
25°	23342
30°	19047
35°	15305
40°	12108
45°	9559
50°	7471
55°	5849
60°	4660
65°	3749
70°	2725
75°	1440
80°	1073
85°	566

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9559 cd/sqm



TEST NUMBER: P641206

CATALOG NUMBER: ML5612LSNFL2597FS1E - 694WB - 600LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.3	19.2
10°-20°	239.9	25.8
20°-30°	177.8	19.1
30°-40°	143.6	15.4
40°-50°	96.1	10.3
50°-60°	55.8	6.0
60°-70°	29.2	3.1
70°-80°	8.5	0.9
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	597.0	64.1
0°-40°	740.5	79.5
0°-60°	892.4	95.8
0°-90°	931.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	931.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2286	
5°	2079	179
15°	833	240
25°	386	178
35°	229	144
45°	123	96
55°	61	56
65°	29	29
75°	7	9
85°	1	1
90°	0	



TEST NUMBER: P641206

CATALOG NUMBER: ML5612LSNFL2597FS1E - 694WB - 600LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2285.8
2.5°	2238.2
5°	2079.2
7.5°	1814.0
10°	1491.8
12.5°	1149.3
15°	833.1
17.5°	617.1
20°	496.4
22.5°	432.7
25°	385.9
27.5°	341.7
30°	300.9
32.5°	263.5
35°	228.7
37.5°	197.2
40°	169.2
42.5°	145.4
45°	123.3
47.5°	103.7
50°	87.6
52.5°	73.1
55°	61.2
57.5°	51.0
60°	42.5
62.5°	35.7
65°	28.9
67.5°	23.8
70°	17.0
72.5°	11.1
75°	6.8
77.5°	4.3
80°	3.4
82.5°	1.7
85°	0.9
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)