

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641793

Luminaire Tested: ML5612LSVWFL97FS1E - 692SC - 600LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641793  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-106)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSVWFL97FS1E - 692SC - 600LM - 3500K  
Description: ML56 RR, MILKY OPTIC, 6" SPECULAR CLEAR TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 930.8 lumens  
Efficiency: N/A  
Efficacy: 90.4 lumens/watt  
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.69  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641793  
CATALOG NUMBER: ML5612LSVWFL97FS1E - 692SC - 600LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P641793

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692SC - 600LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	93	105	100	96	92	97	93	90	93	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			78																
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71			71																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	70	67	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	58	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			49																
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46			46																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	72406
5°	67686
10°	55354
15°	42100
20°	33620
25°	28659
30°	25213
35°	22506
40°	19172
45°	13521
50°	7897
55°	4129
60°	1875
65°	584
70°	144
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13521 cd/sqm



TEST NUMBER: P641793

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692SC - 600LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	109.7	11.8
10°-20°	209.1	22.5
20°-30°	219.3	23.6
30°-40°	209.2	22.5
40°-50°	135.0	14.5
50°-60°	41.9	4.5
60°-70°	6.2	0.7
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	538.2	57.8
0°-40°	747.4	80.3
0°-60°	924.3	99.3
0°-90°	930.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	930.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1321	
5°	1230	110
15°	742	209
25°	474	219
35°	336	209
45°	174	135
55°	43	42
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P641793

CATALOG NUMBER: ML5612LSVWFL97FS1E - 692SC - 600LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1320.8
2.5°	1297.4
5°	1230.0
7.5°	1123.0
10°	994.4
12.5°	860.5
15°	741.8
17.5°	649.2
20°	576.3
22.5°	520.6
25°	473.8
27.5°	434.3
30°	398.3
32.5°	366.8
35°	336.3
37.5°	305.7
40°	267.9
42.5°	223.0
45°	174.4
47.5°	129.5
50°	92.6
52.5°	63.8
55°	43.2
57.5°	27.9
60°	17.1
62.5°	9.9
65°	4.5
67.5°	1.8
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)