

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641248

Luminaire Tested: ML5612LSVWFL7597FS1E - 592H - 1200LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-72)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL7597FS1E - 592H - 1200LM - 3500K
Description: ML56 RR, 75D TIR OPTIC, 5" HAZE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1507.1 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.07
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641248

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592H - 1200LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P641248

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592H - 1200LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20									
RC	80					70					50					30					10					0				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100												
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93												
2	107	101	97	93	105	100	96	92	96	93	90	93	91	88	91	88	87	85												
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78												
4	95	87	81	76	93	85	80	75	83	78	75	81	77	74	79	76	73	71												
5	89	80	74	69	88	79	73	69	77	72	68	76	71	68	74	70	67	65												
6	84	74	68	63	83	74	67	63	72	67	63	71	66	62	69	65	62	60												
7	79	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55												
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51												
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48												
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88556
5°	89227
10°	90483
15°	92710
20°	93063
25°	88356
30°	79112
35°	63604
40°	42127
45°	20720
50°	12170
55°	7102
60°	2416
65°	523
70°	323
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20720 cd/sqm



TEST NUMBER: P641248

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592H - 1200LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.5	7.1
10°-20°	319.6	21.2
20°-30°	461.7	30.6
30°-40°	403.1	26.7
40°-50°	162.0	10.7
50°-60°	47.5	3.2
60°-70°	5.1	0.3
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	888.9	59.0
0°-40°	1292.0	85.7
0°-60°	1501.5	99.6
0°-90°	1507.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1507.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1122	
5°	1126	108
15°	1134	320
25°	1014	462
35°	660	403
45°	186	162
55°	52	47
65°	3	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P641248

CATALOG NUMBER: ML5612LSVWFL7597FS1E - 592H - 1200LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1121.8
2.5°	1123.2
5°	1126.0
7.5°	1127.4
10°	1128.8
12.5°	1131.6
15°	1134.4
17.5°	1128.8
20°	1107.8
22.5°	1068.8
25°	1014.4
27.5°	947.4
30°	867.9
32.5°	771.6
35°	660.0
37.5°	533.0
40°	408.8
42.5°	287.4
45°	185.6
47.5°	127.0
50°	99.1
52.5°	72.6
55°	51.6
57.5°	33.5
60°	15.3
62.5°	8.4
65°	2.8
67.5°	1.4
70°	1.4
72.5°	1.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)